
TECHNICAL DATA SHEET

Terminals, pin

Vinyl-insulated, double crimp

Spec-Kon[®]



Features:

- Easy entry double crimp
- Corrosive resistant plating
- Color coded to wire size range

Maximum rating:

- 75°C Max
- 600 volts
- Copper conductors only

Application tool:

- ERG9004

Vinyl-insulated pin terminals for wire termination of copper conductors ranging from 0.5mm² to 6mm²

Certifications / Standards:



Conforms to:

- IEC 60352-2

Materials / Finishes:

- Copper terminal
- Electro-Tin plated
- Vinyl insulation

Terminals, pin:
Vinyl-insulated, double crimp

Product selection

Drawing	Part no:	Wire size range (mm ²)	Color	Dimensions (mm)				Crimping tool
				L	F	W	D	
	P1.5-19VDC	0.5-1.5	Red	18.8	9.0	1.9	4.3	ERG9004
	P1.5-20VDC	0.5-1.5	Red	19.8	10.0	1.9	4.3	
	P1.5-22VDC	0.5-1.5	Red	21.8	12.0	1.9	4.3	
	P1.5-23VDC	0.5-1.5	Red	22.8	13.0	1.9	4.3	
	P2.5-19VDC	1.5-2.5	Blue	18.8	9.0	1.9	4.8	
	P2.5-20VDC	1.5-2.5	Blue	19.8	10.0	1.9	4.8	
	P2.5-22VDC	1.5-2.5	Blue	21.8	12.0	1.9	4.8	
	P2.5-23VDC	1.5-2.5	Blue	22.8	13.0	1.9	4.8	
	P2.5-24VDC	1.5-2.5	Blue	23.8	14.0	1.9	4.8	
	P2.5-25VDC	1.5-2.5	Blue	24.8	15.0	1.9	4.8	
	P2.5-26VDC	1.5-2.5	Blue	26.0	16.0	1.9	4.8	
	P6-23VDC	4.0-6.0	Yellow	23.0	10.0	2.8	6.7	
	P6-25VDC	4.0-6.0	Yellow	25.0	12.0	2.8	6.7	
	P6-26VDC	4.0-6.0	Yellow	26.0	13.0	2.8	6.7	

Note: Products must be installed in accordance with applicable national and local electrical codes.