

PRODUCT SPECIFICATION

STXXW3LS1

Daylite Self-Contained Opal IP65 Self-Test Surface

Catalogue Number **STXXW3LS1**
 GID **7TCA091160R0574**
 Warranty **3 Year/s Refer to ABB warranty terms & conditions**
 Power Supply System **Self-Contained (individual battery)**
 Mounting Method/Form **Ceiling, Wall Surface**
 Housing Material **Plastic**
 Colour **White**
 Dimensions (LxWxD) **342 x 98 x 72 mm**
 Temperature Range **0 to 30°C**
 Weight **0.75 Kg**

Emergency Duration (Hours) **3 Hours**
 Battery **NiCd**
 Monitoring Equipment **Automatic self test**
 Lamp **1 x 2W LED**
 Emergency Light Output (Lumens) **214**
 Average Lifespan light source (Hours) **100000 Hours**
 Light Colour/Temperature/CRI **White / 4000 / 80**
 Degree of Protection **IP65 IK10**

Type of Legend **Single Sided**
 Exit Sign Viewing/Recognition Distance (m) **23**
 Nominal Voltage **220-240v AC 50/60Hz**
 Power Consumption **6.1 VA / 3.9 Watts**
 Current **Nominal: 25.5mA (mA) Inrush: 0.7A**

Accessories

- RSEN2X** Down ISO7010 Legend
- RSEN3X** Left ISO7010 Legend
- RSEN6X** Right ISO7010 Legend
- RSEN5X** Up ISO7010 Legend
- RSB1X** Arabic English Legend

XTR Semi-recessing bezel White



Exit Sign
STXXW3LS1 + RSEN5X



Bulkhead
STXXW3LS1

