

PRODUCT SPECIFICATION

# WWA8LS1X

## Weatherforce 24-50v AC/DC 27M IP65 Surface

Catalogue Number **WWA8LS1X**  
GID **7TCA091130R0554**  
Warranty **3 Year/s Refer to ABB warranty terms & conditions**  
Power Supply System **Mains / Slave Operation**  
Mounting Method/Form **Ceiling, Wall Surface**  
Housing Material **Metal**  
Colour **White**  
Dimensions (LxWxD) **400 x 140 x 100 mm**  
Temperature Range **0 to 40°C**  
Weight **1.2 Kg**

Emergency Duration (Hours) **Central Battery Hours**  
Battery **Central Battery**  
Monitoring Equipment **None**  
Lamp **1 x 1W LED**  
Emergency Light Output (Lumens) **207**  
Average Lifespan light source (Hours) **100000 Hours**  
Light Colour/Temperature/CRI **White / 4000 / 80**  
Degree of Protection **IP65 IK10**

Type of Legend **Single or Double Sided**  
Exit Sign Viewing/Recognition Distance (m) **27**  
Nominal Voltage **24-50v AC/DC 0-60Hz**  
Power Consumption **3.4 VA / 2.1 Watts**  
Current **Nominal: 57mA (mA) Inrush: 1.1A**

### Accessories

**XEN2/2DV32** Double sided Diffuser with Down+Down ISO7010 Legend  
**XEN3/6DV32** Double sided Diffuser with Left+Right ISO7010 Legend  
**XEN5/5DV32** Double sided Diffuser with Up+Up ISO7010 Legend

**XB10DV32** Double sided Diffuser with Blank+Arabic English Legend  
**XB11DV32** Double sided Diffuser with Arabic English+Arabic English Legend  
**XB23DV32** Double sided Diffuser with Arabic English Left+Arabic English Right Legend  
**XB50DV32** Double sided Diffuser with Blank+Arabic English Up Legend  
**XB66DV32** Double sided Diffuser with Arabic English Down+Arabic English Down Legend

**BBZ** Semi recessing bezel White



Double Sided Exit Sign  
WWA8LS1X + XEN2/2DV32

