

PRODUCT SPECIFICATION

CTSR2-DSB-M3

Serenga 2 Self-Contained Spotlite IP42 Naveo Recess

Catalogue Number **CTSR2-DSB-M3**

GID **7TCA091180R0370**

Warranty **4 Year/s Refer to ABB warranty terms & conditions**

Power Supply System **Self-Contained (individual battery)**

Mounting Method/Form **Ceiling Recessed**

Housing Material **Aluminium/Plastic**

Colour **White**

Dimensions (LxWxD) **226 x 100 x 38 mm**

Temperature Range **5 to 40°C**

Weight **0.581 Kg**

Emergency Duration (Hours) **3 Hours**

Battery **NiMH**

Monitoring Equipment **Naveo®Pro**

Lamp **1 x 2W LED**

Emergency Light Output (Lumens) **203**

Average Lifespan light source (Hours) **100000 Hours**

Light Colour/Temperature/CRI **White / 5600 / 70**

Degree of Protection **IP42**

Type of Legend **Not Applicable**

Exit Sign Viewing/Recognition Distance (m) **Not Applicable**

Nominal Voltage **220-240v AC 50Hz**

Power Consumption **3.5 VA / 3 Watts**

Current **Nominal: 15mA (mA)**

Accessories

SR2-LENS1 Lens A Escape route 2-4M Ceiling mount

SR2-LENS2 Lens B Escape route 4-8M Ceiling mount OR Spot 2-4M

Ceiling mount

SR2-LENS3 Lens C Escape route 8-12M Ceiling mount

SR2-LENS4 Lens D Open Area 2-4M Ceiling mount

SR2-LENS5 Lens E Open Area 4-8M Ceiling mount

SR2-LENS6 Lens E Open Area 8-12M Ceiling mount

SR2-LENS7 Lens G Escape route 2-4M Wall mount

