Left Side View



Front View



Right Side View



Notes

1) FINISH: GRAY
2) CABINET: 16 GA GALV. STEEL
3) 200AMP CONTINUOUS,
   600 VAC, 1 PHASE, 3 WIRE
4) FOR BROOKS OR INNER-TITE STANDARD LENGTH BARREL LOCK IN CONJUNCTION WITH A BROOKS LOCK GUARDS #865 OR #86505, WITH A PERMANENTLY WELDED BRACKET.
5) MIDWEST LABEL ATTACHED TO THE END OF THE CARTON.
6) TEMPORARY CARDBOARD METER OPENING COVER PROVIDED.
7) MIDWEST LOGO LOCATED IN THE LOWER LEFT-HAND CORNER OF THE FRONT.
8) STACK FLAT ON 36 X 48 PALLET. (DO NOT STACK ON SIDES)

Bottom View



METER SKT –(1) 200A 600V 1P3W N3R G90 4-TERM HRN BYP TRIPLX GRD SMALL HUBCVR PLT AEP BARREL LK TOP/BOT FED

CAT NO	DWG DATE	REV #
MEPKS1CS1DTV	02/10/2016	01