

PRODUCT SPECIFICATION

# DAEGR3LS1-S22

## Guideway Self-Contained 22M IP40 DALI Test Recess

Catalogue Number **DAEGR3LS1-S22**  
 GID **7TCA091180R0340**  
 Warranty **4 Year/s Refer to ABB warranty terms & conditions**  
 Power Supply System **Self-Contained (individual battery)**  
 Mounting Method/Form **Ceiling, Wall Recessed**  
 Housing Material **Aluminium/Plastic**  
 Colour **Silver**  
 Dimensions (LxWxD) **235 x 84 x 134 mm**  
 Temperature Range **5 to 35°C**  
 Weight **1.2 Kg**

Emergency Duration (Hours) **3**  
 Battery **NiMH**  
 Monitoring Equipment **DALI test**  
 Lamp **1 x 2W LED**  
 Emergency Light Output (Lumens) **Not Applicable**  
 Average Lifespan light source (Hours) **100000 Hours**  
 Light Colour/Temperature/CRI **White / 5000 / 80**  
 Degree of Protection **IP40**

Type of Legend **Single or Double Sided**  
 Exit Sign Viewing/Recognition Distance (m) **22**  
 Nominal Voltage **220-240v AC 50Hz**  
 Power Consumption **4.4 VA / 4 Watts**  
 Current **Nominal: 19mA (mA)**

### Accessories

- XEN2EG22** Down ISO7010 Legend Single Sided
- XEN3EG22** Left ISO7010 Legend Single Sided
- XEN6EG22** Right ISO7010 Legend Single Sided
- XEN5EG22** Up ISO7010 Legend Single Sided
- XBN1EG22** Arabic English Legend Single Sided
- XEN0G22** Blank Legend Single Sided

**EG-T4EG** Cover Discs (2x semi-circular, 2x rectangular) for Slave

- EG-TKIT50** Suspension Kit Pendant 50mm
- EG-TKIT100** Suspension Kit Pendant 100mm
- EG-WKIT150** Wire Suspension Kit 150mm

- XEN602EG22** Down ISO7010 Legend Flag Mount
- XEN603EG22** Left ISO7010 Legend Flag Mount
- XEN606EG22** Right ISO7010 Legend Flag Mount
- XEN605EG22** Up ISO7010 Legend Flag Mount



**Exit Sign Suspended**  
DAEGR3LS1-S22 + EG-WKIT150



**Exit Sign Recessed**  
DAEGR3LS1-S22

