

A



B

C

D

E

F



Tolerance class according to ISO 2768-1 (Partly):
 Toleranseklasse i h.h.t. NS-ISO 2768-1 (Utdrag):
 "Medium" "Rough"
 "Middels" "Grov"
 For dette dokument og den her viste gjenstand forbeholder vi oss alle rettigheter. Mangfoldiggjørelse, offentliggjørelse til tredjemann eller utnyttelse av deres innhold er uten vår uttrykkelige tillatelse forbudt. ©ABB AS.

Tillatte avvik for basisområdet/Permissible deviations for basic range						
Bestemmelse	6	6-30	30-120	120-400	400-1000	1000-2000
Middels	± 0.1	± 0.2	± 0.3	± 0.5	± 0.8	± 1.2
Grov	± 0.2	± 0.5	± 0.8	± 1.2	± 1	± 1

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden. ©ABB AS.

A	25.12.2015 JQ	New drawing			
Prepared Utført	25.12.2015 JQ	Resp. dep. Ansv. avd.	Technology	Title Tittel	
Approved Kontroll.		Take over dep. Overtagersted		BZ_2000A-1P-M12 Dimensional drawing	Language Språk E
Released Brukskl.		Revision Endring	A 25.12.2015 JQ	Scale Målestokk	A3/1:5
			BOM on Drawing		No. o. sheets Ant. blad 1
ABB AS Division Low Voltage Products Skien Norway				Document No. Tegning nr.	1SEB000431
					Sheet no. Blad nr. 1

A

B

C

D

E

F