

PRODUCT SPECIFICATION

# SR2-SA230LT-D1

## Serenga 2 230v AC Open Area IP54 EMEX Test Surface

Catalogue Number **SR2-SA230LT-D1**  
GID **7TCA091180R0239**

Warranty **4 Year/s Refer to ABB warranty terms & conditions**

Power Supply System **Mains / Slave Operation**

Mounting Method/Form **Ceiling Surface**

Housing Material **Aluminium/Plastic**

Colour **White**

Dimensions (LxWxD) **150 x 150 x 35 mm**

Temperature Range **0 to 40°C**

Weight **0.745 Kg**

Nominal Voltage **220-240v AC 50/60Hz**

Emergency Duration (Hours) **Mains / Central Battery Hours**

Battery **Mains / Central Battery**

Monitoring Equipment **EMEX test**

Lamp **1 x 2W LED**

Light output in Emergency Operation **203 Lumens**

Average Lifespan light source (hours) **100000 Hours**

Light Colour/Temperature/CRI **White / 5600 / 70**

Degree of Protection **IP 54 IK tbc**

Wiring System **Mains / CBU**

Type of Legend **Not Applicable**

Exit Sign Viewing/Recognition Distance (m) **Not Applicable**

Power Consumption **5.5 VA / 5 Watts**

Nominal Current **24 (mA)**

Inrush Current **tbc A to 0.1 ms**

### Accessories

**SR2-LENS1** Lens A Escape route 2-4M Ceiling mount

**SR2-LENS2** Lens B Escape route 4-8M Ceiling mount OR Spot 2-4M Ceiling mount

**SR2-LENS3** Lens C Escape route 8-12M Ceiling mount

**SR2-LENS4** Lens D Open Area 2-4M Ceiling mount

**SR2-LENS5** Lens E Open Area 4-8M Ceiling mount

**SR2-LENS6** Lens E Open Area 8-12M Ceiling mount

**SR2-LENS7** Lens G Escape route 2-4M Wall mount

