

## Survive-All™ EF41 Series

Class I Division 2, Groups A, B, C and D certified remote fixture



### Description

- Available with single or double lamp heads
- Die-cast aluminum back plate with gasket
- Vandal-resistant UV stabilized polycarbonate lamp cover
- Comes standard with tamper-proof screws and bit
- Universal J-box mounting
- Extreme operational temperature range: -40°F to +104°F (-40°C to +40°C)

### Mounting

- Surface mount
- Conduit entry 1/2" NPT

### Approval

- CSA-US (to UL 924 standards)
- Evaluated to the UL 844 Standard for Class I Division 2, Groups A, B, C and D

### Lamp selection chart and temperature code

Lamp suffix	Voltage	Wattage	Lumens	Replacement #	Temperature code	Max temperature
LA	6	4	200	580.0097-E	T4A	120°C
LB	6	5	415	580.0122-E	T4A	120°C
LG	12	4	220	580.0093-E	T5	100°C
LI	12	5	340	580.0104-E	T4A	120°C
LJ	12	6	540	580.0106-E	T4	135°C
LL	24	4	220	580.0098-E	T5	100°C
LW	120	4	230	580.0113-E	T4A	120°C

### Photometric performance

Lamp	Spacing center-to-center (feet)	
	7' mounting height	15' mounting height
LA	39'	34'
LB	74'	57'
LG	49'	39'
LI	68'	54'
LJ	89'	80'
LL	51'	39'

### How to order

Series	Lamp type/wattage	Color
EF41= Single	(LA)= 6V-4W, MR16 LED	(LJ)= 12V-6W, MR16 LED
EF41D= Double	(LB)= 6V-5W, MR16 LED	(LL)= 24V-4W, MR16 LED
	(LG)= 12V-4W, MR16 LED	(LW)= 120V-4W, MR16 LED
	(LI)= 12V-5W, MR16 LED	

Example: EF41(MJ)-GY

### Warranty

- Five-year limited warranty
- Detailed warranty terms located on page 178 or online at: [www.emergi-lite.com/usa/files/EL\\_Warranty.pdf](http://www.emergi-lite.com/usa/files/EL_Warranty.pdf)

### Dimensions

Dimensions are approximate and subject to change.

