

# Kopex-Ex Brass Fittings & Cable Glands

## Obsolete Stock - Clearance Sale



—  
**ABB Cable Management Products Ltd**  
 CMG House, Station Road Coleshill,  
 Birmingham B46 1HT  
 Tel: +44 (0) 1675 468 217  
 Fax: +44 (0) 1675 468 280  
 E-Mail: sales@kopex.co.uk



Get these competitive prices for a limited time only, offer ends 1st September 2022 - whilst stocks last!

To learn more about Kopex-Ex Brass Glands & Fixings becoming obsolete, you can read the full product change notification [here](#).

—  
**Product Approvals & Ratings**



- **ATEX** Baseefa 16ATX0174X
- **IECEx** IECEx BAS 16.0088X
- **TR-CU** RU C-GB.AA87.B.00198
- **I M2 II 2 GD Ex d e I Mb Ex d e IIC Gb Ex tb IIIC Db**
- **CSA** CSA 060582
- **Class I Div 2 ABCD Class II Div 1 EFG**
- **Temperature Rating:** -60°C to +130°C
- **Ingress Protection Rating:** IP66

—  
**Application**

Kopex-Ex offer a range of glands and fittings that are specially designed and built to offer a superior cable protection solution for the Oil & Gas market, as well as other hazardous area applications. Manufactured to meet ATEX and IECEx standards, they are designed to be robust and to meet the demands of dangerous environments.

Constructed from brass with an epoxy resin barrier, these glands and fittings are high specification solutions, ideal for all hazardous area applications.

## ABB Kopex-Ex Pricelist

### Special Clearance Stock Pricing 2022

Before placing order for lot price,  
please contact our customer service team on  
the following email address as you may be  
entitled to a better discount:

For UK: cmgukcustomerservice@gb.abb.com

For Europe: la\_l\_customerservice@be.abb.com

Part No.	MOQ	Lot Qty	Promotional selling price, MOQ			Promotional selling price, lot		
			USD/MOQ	EUR/MOQ	GBP/MOQ	USD/Lot	EUR/Lot	GBP/Lot
EX05AMC2	25	575	\$70.26	€ 59.97	£51.11	\$1,484.03	€ 1,266.65	£1,079.49
EX05MSC1K	1	234	\$6.04	€ 5.15	£4.39	\$1,297.80	€ 1,107.70	£944.03
EX04MLC2K	1	212	\$2.84	€ 2.42	£2.06	\$552.02	€ 471.16	£401.54
EX04MSC1	20	200	\$80.31	€ 68.54	£58.41	\$737.50	€ 629.47	£536.46
EX04AMC1K	1	197	\$4.70	€ 4.01	£3.42	\$850.52	€ 725.94	£618.68
EX04MMC1K	1	185	\$4.70	€ 4.01	£3.42	\$798.71	€ 681.72	£580.99
EX05MMC2K	1	180	\$3.55	€ 3.03	£2.58	\$586.22	€ 500.35	£426.42
EX05MMC2	25	175	\$70.26	€ 59.97	£51.11	\$451.66	€ 385.50	£328.54
EX06MMC1K	1	131	\$14.97	€ 12.77	£10.89	\$1,800.58	€ 1,536.84	£1,309.76
EX06MMC2K	1	129	\$5.23	€ 4.47	£3.81	\$620.18	€ 529.34	£451.12
EX03MSC1	20	120	\$80.31	€ 68.54	£58.41	\$442.50	€ 377.68	£321.88
EX03MMC1	15	120	\$61.37	€ 52.38	£44.64	\$450.85	€ 384.81	£327.95
EX05MLC2K	1	107	\$3.70	€ 3.15	£2.69	\$363.12	€ 309.93	£264.14
EX04MMC2K	1	104	\$2.78	€ 2.38	£2.03	\$265.90	€ 226.95	£193.42
EX05MLC1	8	104	\$63.64	€ 54.32	£46.29	\$759.76	€ 648.47	£552.66
EX04AMC2K	1	100	\$2.78	€ 2.38	£2.03	\$255.68	€ 218.22	£185.98
EX04MMC3K	1	100	\$3.34	€ 2.85	£2.43	\$306.63	€ 261.72	£223.05
EX05MSC3K	1	100	\$3.75	€ 3.20	£2.73	\$344.69	€ 294.20	£250.73
EX04MSC1K	1	100	\$4.61	€ 3.94	£3.35	\$423.46	€ 361.43	£308.02
EX04MMC2	50	100	\$98.94	€ 84.44	£71.97	\$181.72	€ 155.10	£132.18
EX04MSC3K	1	100	\$3.12	€ 2.67	£2.27	\$286.76	€ 244.75	£208.59
EX05MMC3K	1	100	\$4.06	€ 3.46	£2.95	\$372.53	€ 317.96	£270.98
EX03MMC2	50	100	\$105.45	€ 90.00	£76.70	\$193.68	€ 165.31	£140.88
EX05AMC2K	1	100	\$3.55	€ 3.03	£2.58	\$325.68	€ 277.97	£236.90
EX04ALC2K	1	100	\$2.84	€ 2.42	£2.06	\$260.39	€ 222.25	£189.41
EX06MSC1	8	96	\$77.58	€ 66.21	£56.43	\$854.94	€ 729.71	£621.89
EX04MMC1	15	90	\$61.37	€ 52.38	£44.64	\$338.13	€ 288.61	£245.96
EX04ALC1K	1	90	\$5.49	€ 4.68	£3.99	\$453.57	€ 387.13	£329.93
EX05ASC1K	1	90	\$6.04	€ 5.15	£4.39	\$499.15	€ 426.04	£363.09
EX05MSC1	15	90	\$79.55	€ 67.90	£57.86	\$438.32	€ 374.12	£318.84
EX04MLC1	15	90	\$72.73	€ 62.08	£52.90	\$400.75	€ 342.05	£291.51
EX06MLC2K	1	84	\$5.38	€ 4.59	£3.91	\$414.67	€ 353.93	£301.63

## ABB Kopex-Ex Pricelist

### Special Clearance Stock Pricing 2022

Before placing order for lot price,  
please contact our customer service team on  
the following email address as you may be  
entitled to a better discount:

For UK: cmgukcustomerservice@gb.abb.com

For Europe: la\_l\_customerservice@be.abb.com

Part No.	MOQ	Lot Qty	Promotional selling price, MOQ			Promotional selling price, lot		
			USD/MOQ	EUR/MOQ	GBP/MOQ	USD/Lot	EUR/Lot	GBP/Lot
EX05MLC3K	1	70	\$4.62	€ 3.94	£3.36	\$296.95	€ 253.45	£216.00
EX05ALC2K	1	70	\$3.70	€ 3.15	£2.69	\$237.56	€ 202.76	£172.80
EX06MSC3K	1	70	\$5.87	€ 5.01	£4.27	\$377.28	€ 322.02	£274.44
EX05MMC1	10	70	\$58.33	€ 49.79	£42.43	\$375.01	€ 320.08	£272.79
EX05MMC1K	1	70	\$6.60	€ 5.63	£4.80	\$424.18	€ 362.04	£308.55
EX04MC5	1	69	\$52.83	€ 45.09	£38.43	\$3,347.50	€ 2,857.17	£2,435.00
EX05ALC1	8	62	\$303.57	€ 259.10	£220.82	\$2,160.61	€ 1,844.13	£1,571.65
EX05ALC3	20	60	\$77.64	€ 66.26	£56.47	\$213.89	€ 182.56	£155.59
EX05ASC1	15	60	\$71.93	€ 61.40	£52.33	\$264.25	€ 225.54	£192.22
EX05ASC3K	1	56	\$3.75	€ 3.20	£2.73	\$193.03	€ 164.75	£140.41
EX05ALC1K	1	50	\$8.76	€ 7.48	£6.37	\$402.38	€ 343.44	£292.69
EX06AMC1K	1	50	\$14.97	€ 12.77	£10.89	\$687.25	€ 586.58	£499.91
EX06ASC1K	1	50	\$10.81	€ 9.23	£7.86	\$496.34	€ 423.64	£361.05
EX05AMC1	10	50	\$58.33	€ 49.79	£42.43	\$267.86	€ 228.63	£194.85
EX05MLC1K	1	43	\$8.76	€ 7.48	£6.37	\$346.04	€ 295.36	£251.71
EX06MMC3K	1	40	\$7.18	€ 6.13	£5.22	\$263.83	€ 225.18	£191.91
EX07MSC3K	1	40	\$10.56	€ 9.01	£7.68	\$387.82	€ 331.01	£282.10
EX07MMC2K	1	33	\$10.67	€ 9.10	£7.76	\$323.22	€ 275.87	£235.11
EX07MSC1K	1	25	\$21.25	€ 18.14	£15.46	\$487.92	€ 416.45	£354.92
EX06MMC1	5	25	\$68.34	€ 58.33	£49.71	\$313.78	€ 267.82	£228.25
EX07MLC2K	1	25	\$10.92	€ 9.32	£7.94	\$250.69	€ 213.97	£182.35
EX07MSC1	5	25	\$97.41	€ 83.14	£70.85	\$447.27	€ 381.75	£325.35
EX04MLC1K	1	22	\$5.49	€ 4.68	£3.99	\$110.87	€ 94.63	£80.65
EX08MMC2K	1	20	\$16.24	€ 13.87	£11.82	\$298.37	€ 254.66	£217.04
EX07MMC1	3	18	\$65.59	€ 55.98	£47.71	\$361.39	€ 308.46	£262.88
EX07MMC3K	1	18	\$12.43	€ 10.61	£9.04	\$205.53	€ 175.42	£149.50
EX05MLC2	15	15	\$44.39	€ 37.89	£32.29	\$40.77	€ 34.80	£29.65
EX08MSC1	2	12	\$63.49	€ 54.19	£46.19	\$349.86	€ 298.62	£254.49
EX08MMC1K	1	12	\$37.25	€ 31.79	£27.09	\$410.46	€ 350.33	£298.57
EX08MSC3K	1	12	\$16.62	€ 14.18	£12.09	\$183.12	€ 156.29	£133.20
EX09MSC3K	1	12	\$26.09	€ 22.27	£18.98	\$287.49	€ 245.38	£209.12
EX08MMC3K	1	12	\$19.08	€ 16.29	£13.88	\$210.31	€ 179.51	£152.98

## ABB Kopex-Ex Pricelist

### Special Clearance Stock Pricing 2022

Before placing order for lot price,  
please contact our customer service team on  
the following email address as you may be  
entitled to a better discount:

For UK: cmgukcustomerservice@gb.abb.com

For Europe: la1\_customerservice@be.abb.com

Part No.	MOQ	Lot Qty	Promotional selling price, MOQ			Promotional selling price, lot		
			USD/MOQ	EUR/MOQ	GBP/MOQ	USD/Lot	EUR/Lot	GBP/Lot
EX08MMC1	2	12	\$68.57	€ 58.53	£49.88	\$377.85	€ 322.51	£274.85
EX08MSC1K	1	11	\$34.69	€ 29.61	£25.23	\$350.45	€ 299.12	£254.92
EX09MSC1	2	10	\$106.16	€ 90.61	£77.22	\$487.48	€ 416.07	£354.59
EX09MMC3K	1	10	\$25.94	€ 22.14	£18.87	\$238.25	€ 203.35	£173.31
EX09MSC1K	1	9	\$56.50	€ 48.22	£41.10	\$466.98	€ 398.57	£339.68
EX09MMC1K	1	9	\$61.37	€ 52.38	£44.64	\$507.22	€ 432.92	£368.95
EX09MMC1	1	8	\$57.91	€ 49.42	£42.12	\$425.43	€ 363.12	£309.46
EX07MMC1K	1	7	\$23.76	€ 20.28	£17.29	\$152.76	€ 130.38	£111.12
EX08ASC1	2	6	\$63.49	€ 54.19	£46.19	\$174.93	€ 149.31	£127.25
EX05AMC1K	1	1	\$6.60	€ 5.63	£4.80	\$6.06	€ 5.17	£4.41
EX10MSC1	1	8	\$97.78	€ 83.46	£71.13	\$718.39	€ 613.16	£522.56
EX10MSC1K	1	8	\$107.35	€ 91.62	£78.08	\$788.67	€ 673.15	£573.68
EX10MMC1	1	6	\$104.76	€ 89.42	£76.21	\$577.27	€ 492.72	£419.91
EX10MMC1K	1	5	\$114.45	€ 97.68	£83.25	\$525.52	€ 448.54	£382.27
EX10MMC2	1	3	\$36.28	€ 30.97	£26.39	\$99.96	€ 85.31	£72.71
EX/M25/SER	10	680	\$7.53	€ 6.43	£5.48	\$470.24	€ 401.36	£342.06
EX/M32/SER	10	500	\$13.79	€ 11.77	£10.03	\$633.34	€ 540.57	£460.69
EX/M20/SER	10	440	\$4.55	€ 3.88	£3.31	\$183.85	€ 156.92	£133.73
EX/M32/C	5	115	\$26.52	€ 22.63	£19.29	\$560.13	€ 478.08	£407.44
EX/075-M20/TC	5	35	\$32.95	€ 28.12	£23.97	\$211.80	€ 180.78	£154.07
EX/M40-M20/R	5	35	\$44.33	€ 37.84	£32.25	\$284.98	€ 243.24	£207.30
EX/M40-M25/R	5	30	\$40.35	€ 34.44	£29.35	\$222.32	€ 189.76	£161.72
EX/M25-M32/E	5	20	\$31.97	€ 27.29	£23.25	\$117.44	€ 100.24	£85.43
EX/075/C	5	15	\$18.97	€ 16.19	£13.80	\$52.27	€ 44.61	£38.02
EX/050-M20/TC	5	10	\$25.24	€ 21.54	£18.36	\$46.36	€ 39.57	£33.72
EX/M16-M20/E	5	10	\$19.85	€ 16.94	£14.44	\$36.45	€ 31.11	£26.52
EX/M40-M32/R	5	10	\$38.54	€ 32.89	£28.03	\$70.78	€ 60.41	£51.49
EX/M32-M25/R	5	5	\$20.94	€ 17.88	£15.23	\$19.23	€ 16.42	£13.99
HAM0505G1	1	33	\$21.49	€ 18.34	£15.63	\$651.33	€ 555.93	£473.79
HAM0304G1	1	30	\$22.44	€ 19.15	£16.32	\$618.31	€ 527.74	£449.76
HAM0404G1	1	38	\$17.77	€ 15.16	£12.92	\$620.02	€ 529.20	£451.01
HAM0606G1	1	8	\$30.24	€ 25.81	£22.00	\$222.19	€ 189.64	£161.62