



24 SVK 3

Central 24 volt AC/DC emergency power supply for a connected load of 560 watt for a duration of 1 hour, 4 circuits non-maintained + 4 circuits maintained

Product Information

Type	24 SVK 3
Catalog number	11111053
Category_	24 Volt
GTIN	08713812746067
GID	7TCA091310R0014
Serie	24 SVK
Warranty (Year)	2
Other	This central emergency power supply can be customized to your specification please contact the customer support department at telephone 088 2600900 for more information.



Characteristics

Mounting Method	Wall
Material housing	Steel
Colour housing	Gray
Material	Steel
Colour	Gray
Length (mm)	800
Width (mm)	800
Height/depth (mm)	300
Nominal voltage (V)	230
Voltage type	AC
Duration (hours)	1
Type of load	Ohms
Power (W)	560
Monitoring equipment	Automatic self test
Output voltage (V)	24 AC/DC
Number of circuits	8
Circuit fuse (A)	10
Protection class	I
Degree of protection (IP)	20
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Temperature range (°C)	5 ~ +20

Article Details

Product class	Emergency lighting power supply unit
E-code	EC002678
Discount group	30411
Harmonized code	8537109900
GLN	8713812000008

Ordering information

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1

Order Increment	1
-----------------	---

Supply Information

Weight (kg)	100
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	300 x 800 x 800