



## TA 725/HF/LED

Slave led 230 Volt, maintained surface mount led luminaire for large viewing distance (56 meter), series Alulux

### Product Information

Type	TA 725/HF/LED
Catalog number	11112088
Category_	Escape route signalisation
GTIN	08713812759869
GID	7TCA091130R0333
Serie	Alulux
Warranty (Year)	5



### Characteristics

Power supply system	Central
Continuous operation	Yes
Mounting Method	Wall
Mounting form	Surface
Material housing	Aluminium
Colour housing	Aluminium
Material cover	Plastic, opal
Material	Aluminium
Colour	Aluminium
Length (mm)	725
Width (mm)	300
Height/depth (mm)	100
Nominal voltage (V)	230
Voltage type	AC/DC
Monitoring equipment	None
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	2
Number of lamps	4
Average lifespan light source (hours)	100.000
Colour of light	White
Colour temperature (K)	6350
Protection class	I
Degree of protection (IP)	20
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Single / double-sided
Labelling type	Insert sheet/plate
Recognition distance (m)	56
Circuit	Other
Power consumption maintained mode (W)	19,5
Apparent power consumption maintained mode (VA)	33,5
Nominal current (mA)	143
Inrush Current (A - 0.1ms)	14,2
Powerfactor	0,58
Temperature range (°C)	5 ~ +25

### Article Details

Product class	Emergency luminaire
E-code	EC001957
Discount group	30405
Harmonized code	9405408440
GLN	8713812000008

**Ordering information**

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

**Supply Information**

Weight (kg)	3,483
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	810 x 310 x 125