

Conversie pictogrammen NEN 6088 > NEN 3011

(NEN 6088 en NEN 3011)	Folie 0,5 mm	Inlegfolie 0,3 mm			Inlegfolie 0,35 mm	Zelfklevende folie 0,1 mm				Lexan 2 mm	Opaal PET-G 3 mm			Helder perspex (XT) 8 mm		
L x H (mm)	326x180	292x140	296x162	231x126	302x127	275x117	295x105	320x120	525x105	222x113	322x163	320x137	261x137	675x295	315x175	315x175
Type	IL(N) OL(N)	SER-FC(X) SER-FO(X)	SER-FI(X)	PRE	AQL 02 AQL 08	AQL/DZ (C/D)DZ (C/D)IB 325 FM(N)-TRV	XION (D)VA 360 NB(N)	IND 08 NBN WD TN(A)T	(D)VA 590 IND 18 NB(N) 13	EVAGO	EVAGO	TA-TL 400 WER	(D)TA 330	(D)TA 725	ITA	IL(N) OL(N)
Rechtdoor	P 4	P 4-SER-C	P 4-SER-I	P4-PRE	PSA 4	TS 275/19	TS 295/19	TS 320/19	TS 525/19	PP 220/4	PP 320/4	PP 400/3	PP 300/3	PP 725/4	PPT 315/4/BL	PP(L) 315/4/BL
	P 51	P 51-SER-C	P 51-SER-I	P51-PRE	PSA 51	TS 275/51	TS 295/51	TS 320/51	TS 525/51	PP 220/51	PP 320/51	PP 400/51	PP 300/51	PP 725/51	PPT 315/51/BL	PP(L) 315/51/BL
Rechts	P 5	P 5-SER-C	P 5-SER-I	P5-PRE	PSA 5	TS 275/11	TS 295/11	TS 320/11	TS 525/11	PP 220/5	PP 320/5	PP 400/2	PP 300/2	PP 725/2	PPT 315/5/BL	PP(L) 315/5/BL
	P 52	P 52-SER-C	P 52-SER-I	P52-PRE	PSA 52	TS 275/52	TS 295/52	TS 320/52	TS 525/52	PP 220/52	PP 320/52	PP 400/52	PP 300/52	PP 725/52	PPT 315/52/BL	PP(L) 315/52/BL
Links	P 6	P 6-SER-C	P 6-SER-I	P6-PRE	PSA 6	TS 275/10	TS 295/10	TS 320/10	TS 525/10	PP 220/6	PP 320/6	PP 400/1	PP 300/1	PP 725/1	PPT 315/6/BL	PP(L) 315/6/BL
	P 53	P 53-SER-C	P 53-SER-I	P53-PRE	PSA 53	TS 275/53	TS 295/53	TS 320/53	TS 525/53	PP 220/53	PP 320/53	PP 400/53	PP 300/53	PP 725/53	PPT 315/53/BL	PP(L) 315/53/BL
Beneden	P 4	P 4-SER-C	P 4-SER-I	P4-PRE	PSA 4	TS 275/4	TS 295/19	TS 320/19	TS 525/19	PP 220/4	PP 320/4	PP 400/3	PP 300/3	PP 725/4	PPT 315/4/BL	PP(L) 315/4/BL
	P 58	P 58-SER-C	P 58-SER-I	P58-PRE	PSA 58	TS 275/58	TS 295/58	TS 320/58	TS 525/58	PP 220/58	PP 320/58	PP 400/58	PP 300/58	PP 725/58	PPT 315/58/BL	PP(L) 315/58/BL
Boven	P 14	P 14-SER-C	P 14-SER-I	P14-PRE	PSA 14	TS 275/14	TS 295/14	TS 320/14	TS 525/14	PP 220/14	PP 320/14	PP 400/14	PP 300/14	PP 725/14	PPT 315/4/BL	PP(L) 315/14/BL
	P 51	P 51-SER-C	P 51-SER-I	P51-PRE	PSA 51	TS 275/51	TS 295/51	TS 320/51	TS 525/51	PP 220/51	PP 320/51	PP 400/51	PP 300/51	PP 725/51	PPT 315/51/BL	PP(L) 315/51/BL

Pictogramplaten met /BL zijn enkelzijdig bedrukt (achterzijde groen). Indien dubbelzijdige bedrukking gewenst is dan /BL vervangen door /DZ.