

TECHNICAL DATA SHEET - INTERACTIVE PDF

Couplings, three piece

Erickson™ Stainless steel, threaded

T&B® Fittings



Features:

- Free-fitting threads help ensure easy assembly
- Permits coupling conduit without rotating either conduit
- Suitable for concrete-tight application
- Conduit Range ½" to 2"

Applications:

- To couple and effectively bond threaded ends of rigid metal conduit / intermediate metal conduit where neither length of conduit can be rotated

Material / Finishes:

- 316 Stainless Steel

For threaded rigid metal conduit and intermediate metal conduit

Certifications / Standards:



3-Part Specification:
Tools and Calculators

Conforms to:

- UL standard 514B
– File number: E23018

Product selection and dimensions

| Part no. | Conduit Trade size | A inches | B inches |
|-----------|--------------------|----------|----------|
| 675SST | ½" | 1.10" | 1.26" |
| 676SST | ¾" | 1.10" | 1.56" |
| 677SST | 1" | 1.38" | 1.73" |
| 678SST | 1¼" | 1.91" | 2.28" |
| 679SST | 1½" | 1.92" | 2.52" |
| 680SST-TB | 2" | 2.47" | 3.11" |

Note: Product must be installed in accordance with applicable national and local electrical codes.

