



24 SVK 9

Central 24 volt AC/DC emergency power supply for a connected load of 2300 watt for a duration of 1 hour, 10 circuits non-maintained + 10 circuits maintained

Product Information

Type	24 SVK 9
Catalog number	11111059
Category_	24 Volt
GTIN	08713812746128
GID	7TCA091310R0020
Serie	24 SVK
Warranty (Year)	2
Other	The unit comes with a separate plinth 100mm high, overall height when using this plinth 1300mm. This central emergency power supply can be customized to your specification please contact the customer support department at telephone 088 2600900 for more information.



Characteristics

Mounting Method	Standing
Material housing	Steel
Colour housing	Gray
Material	Steel
Colour	Gray
Length (mm)	1200
Width (mm)	800
Height/depth (mm)	400
Nominal voltage (V)	230
Voltage type	AC
Duration (hours)	1
Type of load	Ohms
Power (W)	2.300
Monitoring equipment	Automatic self test
Output voltage (V)	24 AC/DC
Number of circuits	20
Circuit fuse (A)	10
Protection class	I
Degree of protection (IP)	20
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Temperature range (°C)	5 ~ +20

Article Details

Product class	Emergency lighting power supply unit
E-code	EC002678
Discount group	30411
Harmonized code	8537109900
GLN	8713812000008

Ordering information

Orderable	Yes
-----------	-----

Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

Supply Information

Weight (kg)	350
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	400 x 800 x 1200