

PRODUCT SPECIFICATION

IR2WWA3LS1

Weatherforce Self-Contained OPAL IP65 IR2 Surface

Catalogue Number **IR2WWA3LS1**
GID **7TCA091170R0036**
Warranty **3 Year/s Refer to ABB warranty terms & conditions**
Power Supply System **Self-Contained (individual battery)**
Mounting Method/Form **Ceiling, Wall Surface**
Housing Material **Metal/plastic**
Colour **White**
Dimensions (LxWxD) **400 x 140 x 100 mm**
Temperature Range **0 to 30°C**
Weight **1.82 Kg**

Emergency Duration (Hours) **3 Hours**
Battery **NiCd**
Monitoring Equipment **IR2 test**
Lamp **1 x 2W LED**
Emergency Light Output (Lumens) **207**
Average Lifespan light source (Hours) **100000 Hours**
Light Colour/Temperature/CRI **White / 4000 / 80**
Degree of Protection **IP65 IK10**

Type of Legend **Single or Double Sided**
Exit Sign Viewing/Recognition Distance (m) **24**
Nominal Voltage **220-240v AC 50/60Hz**
Power Consumption **6.1 VA / 3.9 Watts**
Current **Nominal: 25.5mA (mA) Inrush: 0.7A**

Accessories

- RSEN2120** Down ISO7010 Legend
- RSEN3120** Left ISO7010 Legend
- RSEN6120** Right ISO7010 Legend
- RSEN5120** Up ISO7010 Legend
- RSEN120** ISO7010 Legend Separate Arrow for Up, Down, Left or Right installation
- RSB1B** Arabic English Legend
- BBZ** Semi recessing bezel White



Exit Sign
IR2WWA3LS1 + RSEN5120



Bulkhead
IR2WWA3LS1

