

PRODUCT SPECIFICATION

# XW8LS1

## Daylite 24-50v AC/DC Opal IP65 Surface

Catalogue Number **XW8LS1**  
GID **7TCA091130R0555**  
Warranty **3 Year/s Refer to ABB warranty terms & conditions**  
Power Supply System **Mains / Slave Operation**  
Mounting Method/Form **Ceiling, Wall Surface**  
Housing Material **Plastic**  
Colour **White**  
Dimensions (LxWxD) **342 x 98 x 72 mm**  
Temperature Range **0 to 40°C**  
Weight **0.56 Kg**

Emergency Duration (Hours) **Central Battery Hours**  
Battery **Central Battery**  
Monitoring Equipment **None**  
Lamp **1 x 1W LED**  
Emergency Light Output (Lumens) **214**  
Average Lifespan light source (Hours) **100000 Hours**  
Light Colour/Temperature/CRI **White / 4000 / 80**  
Degree of Protection **IP65 IK10**

Type of Legend **Single Sided**  
Exit Sign Viewing/Recognition Distance (m) **23**  
Nominal Voltage **24-50v AC/DC 0-60Hz**  
Power Consumption **3.4 VA / 2.1 Watts**  
Current **Nominal: 57mA (mA) Inrush: 1.1A**

### Accessories

**RSEN2X** Down ISO7010 Legend  
**RSEN3X** Left ISO7010 Legend  
**RSEN6X** Right ISO7010 Legend  
**RSEN5X** Up ISO7010 Legend  
**RSB1X** Arabic English Legend

**XTR** Semi-recessing bezel White



Exit Sign  
XW8LS1 + RSEN5X



Bulkhead  
XW8LS1

