

COLOR KEYED® – SHRINK-KON®

Combination copper compression and heat-shrinkable products



01 Dimensions
Frame: 24 in. W x 54 in. H x 24 in. D
Header: 24 in. W x 7 in. H



1. Innovative copper compression solutions
2. Innovative heat-shrinkable solutions

Plan-O-Gram Display unit



A1	A2	A3	A4	A17	A18
A5	A6	A7	A8		
A9	A10	A11	A12	A19	A20
				A21	
A13	A14	A15	A16	A22	A23
				A24	A25
				A26	A27
				A28	A29
				A30	

Refer to Quick-Pop brochure
Template, ELIP Merchandising
for display accessories and shelves.



Side A

Cat. No.	Description	Qty/ Pkg	Order Qty
A1	HS500-1000-4 Heavy-wall tubing*, 4 in, black, 500 - 1000 kcmil	2	2
A2	HS40-400-4 Heavy-wall tubing*, 4 in, black, 2/0 AWG - 350 kcmil	5	5
A3	HS4-30-4 Heavy-wall tubing*, 4 in, black, #1 - 3/0 AWG	5	10
A4	HS6-1-4 Heavy-wall tubing*, 4 in, black, #6 - #12 AWG	5	10
A5	HS12-6-4 Heavy-wall tubing*, 4 in, black, #8 - #6 AWG	5	10
A6	HS16-12-4 Heavy-wall tubing*, 4 in, black, #14 - #10 AWG	5	20
A7	CPO-A-750-48 Thin-wall tubing* + adhesive, 4 in, black, #4 - 3/0 AWG	25	25
A8	CPO-A-500-48 Thin-wall tubing* + adhesive, 4 in, black, #22 - #2 AWG	25	25
A9	CPO-A-375-48 Thin-wall tubing* + adhesive, 4 in, black, #16 - #6 AWG	25	25
A10	CPO-A-250-48 Thin-wall tubing* + adhesive, 4 in, black, #22 - #10 AWG	25	25
A11	CPO-A-187-48 Thin-wall tubing* + adhesive, 4 in, black, #22 - #14 AWG	25	25
A12	CPO-A-125-48 Thin-wall tubing* + adhesive, 4 in, black, #30 - #24 AWG	25	25
A13	CPO187-0-A Thin-wall tubing* + adhesive, 4 in, black, #22 - #14 AWG	25	25
A14	CPO250-0-A Thin-wall tubing* + adhesive, 4 in, black, #22 - #10 AWG	25	25
A15	CPO375-0-A Thin-wall tubing* + adhesive, 4 in, black, #16 - #6 AWG	25	25
A16	CPO500-0-A Thin-wall tubing* + adhesive, 4 in, black, #22 - #2 AWG	25	25
A17	WM-0-45 E-Z-CODE® Wire marker books. Legend: 0 - 45	10	10
A18	WM-A-Z E-Z-CODE® Wire marker books. Legend: A - Z	10	10
A19	AC3X5 Insulating jacket 5 x 3 in	10	50
A20	CPO375-C-6 Thin-wall tubing*, 6 in, transparent, #12 - #6 AWG	20	100
	ou CPO500-C-6 Thin-wall tubing*, transparent, #6 - #1 AWG		50
A21	HS-KIT Thin-wall tubing, black, #14 AWG - 350 kcmil, 6 in	1	5
	or CHS-KIT Thin-wall tubing, 7 colours, #14 AWG - 350 kcmil, 6 in	1	5
A22	MSC250 Motor stub splice insulators 350 - 500 kcmil	2	6
A23	MSC20 Motor stub splice insulators 350 - 500 kcmil	4	8
A24	MSC2 Motor stub splice insulators 350 - 500 kcmil	10	10
A25	MSC8 Motor stub splice insulators 350 - 500 kcmil	10	20
A26	HSC700-1000 Heat-shrinkable end caps 250 - 500 kcmil	5	5
A27	HSC300-600 Heat-shrinkable end caps 2/0 - 350 kcmil	5	10
A28	HSC30-250 Heat-shrinkable end caps #1 - 3/0 AWG	5	20
A29	HSC2-20 Heat-shrinkable end caps #6 - #2 AWG	10	20
A30	HSC8-4 Heat-shrinkable end caps #8 - #6 AWG	10	30

* Heat-shrinkable tubing



B1	B2	B3	B4	B5	B6
B7	B8	B9	B10	B11	B12
B13	B14	B15	B16	B17	B18
B19	B20	B21	B22	B23	B24
B25	B26	B27	B28	B29	B30

Side B

Cat. No.	Description	Qty/ Pkg	Order Qty
B1	54130 Std. barrel, one hole ¼ in. Cu, 8 AWG, #8 weld, 37/24	50	200
B2	54104 Std. barrel, single hole #10 Cu, 8 AWG, #8 weld, 37/24	50	200
B3	54504 Std. barrel splice Cu, 8 AWG, #8 weld, 37/24	50	200
B4	54105 Std. barrel, single hole ¼ in. Cu, 6 AWG, #6 weld, 61/24	50	200
B5	54205 Std. barrel, two hole ¼ in. Cu, 6 AWG, #6 weld, 61/24	50	200
B6	54505 Std. barrel splice Cu, AWG, #6 weld, 61/24	50	200
B7	54106 Std. barrel, single hole ¼ in. Cu, 4 AWG, 91/24	50	100
B8	54140 Std. barrel, single hole ¾ in. Cu, 4 AWG, 91/24	50	100
B9	54506 Std. barrel splice Cu, 4 AWG, 91/24	50	100
B10	54107 Std. barrel, single hole ¼ in. Cu, 2 AWG, #4 weld, 125/24	25	100
B11	54143-TB Std. barrel, single hole ¾ in. Cu, 2 AWG, #4 weld, 125/24	25	100
B12	54507 Std. barrel splice Cu, 2 AWG, #4 weld, 125/24	25	100
B13	54108 Std. barrel, single hole ¼ in. Cu, 1 AWG, #2 weld, 175/24	20	60
B14	54148 Std. barrel, single hole ¾ in. Cu, 1 AWG, #2 weld, 175/24	20	60
B15	54508 Std. barrel splice Cu, 1 AWG, #2 weld, 175/24	20	60
B16	54109 Std. barrel, one hole ¾ in. Cu, 1/0 AWG, #1 weld, 225/24	20	60
B17	54209 Std. barrel, two hole ¾ in. Cu, 1/0 AWG, #1 weld, 225/24	20	60
B18	54509 Std. barrel splice Cu, 1/0 AWG, #1 weld, 225/24	20	60
B19	54110 Std. barrel, one hole ¾ in. Cu, 2/0 AWG, 1/0 weld, 275/24	10	30
B20	54210 Std. barrel, two hole ¾ in. Cu, 2/0 AWG, 1/0 weld, 275/24	10	30
B21	54510 Std. barrel splice Cu, 2/0 AWG, 1/0 weld, 275/24	10	30
B22	54111 Std. barrel, one hole ¾ in. Cu, 2/0 AWG, 2/0 weld, 325/24	10	30
B23	54211 Std. barrel, two hole ¾ in. Cu, 2/0 AWG, 2/0 weld, 325/24	10	30
B24	54511 Std. barrel splice Cu, 2/0 AWG, 2/0 weld, 325/24	10	30
B25	54112 Std. barrel, one hole ¾ in. Cu, 3/0 - 4/0 AWG, 3/0 weld, 450/24	10	20
B26	54212 Std. barrel, two hole ¾ in. Cu, 3/0 - 4/0 AWG, 3/0 weld, 450/24	10	20
B27	54512 Std. barrel splice Cu, 3/0 - 4/0 AWG, 3/0 weld, 450/24	10	20
B28	54113 Std. barrel, one hole ½ in. Cu, 4/0, 250 kcmil	10	20
B29	54275 Std. barrel, two hole ½ in. Cu, 4/0, 250 kcmil	10	20
B30	CP8-TB Kopr-Shield™ Compound	12	12