



## EVA-DOW-32/DALI

Self-contained 4 watt, aluminium surface wall mounted 32 meter led luminaire, including DALI control module, series Evago, including the pictogram PP 320/51

### Product Information

Type	EVA-DOW-32/DALI
Catalog number	4513216953
Category_	Escape route signalisation
GTIN	08713812769493
GID	7TCA091180R0307
Serie	Evago
Warranty (Year)	5
Other	Including DALI communication module, conform EN62386



### Characteristics

Power supply system	Self-contained individual battery
Continuous operation	Yes
Mounting Method	Wall
Mounting form	Surface
Material housing	Aluminium
Colour housing	Aluminium
Material	Aluminium
Colour	Aluminium
Length (mm)	335
Width (mm)	58
Height/depth (mm)	189
Nominal voltage (V)	230
Voltage type	AC
Duration (hours)	1
Battery	NiMH
Monitoring equipment	Safety module for monitoring
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	4
Number of lamps	1
Average lifespan light source (hours)	100.000
Colour of light	White
Colour temperature (K)	5000
CRI	80
Protection class	II
Degree of protection (IP)	40
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Only single-sided
Labelling type	Insert sheet/plate
Recognition distance (m)	32
Circuit	Other
Power consumption maintained mode (W)	6,5
Apparent power consumption maintained mode (VA)	7,1
Nominal current (mA)	31
Powerfactor	> 0,9

Temperature range (°C) 5 ~ +35

**Article Details**

Product class	Emergency luminaire
E-code	EC001957
Discount group	30502
Harmonized code	9405408440
GLN	8713812000008

**Ordering information**

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

**Supply Information**

Weight (kg)	1,578
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	400 x 250 x 88