

PRODUCT SPECIFICATION

# LTCWWA1LS1X

## Weatherforce 230v AC 27M IP65 EMEX Test Surface

Catalogue Number **LTCWWA1LS1X**  
GID **7TCA091140R0543**  
Warranty **3 Year/s Refer to ABB warranty terms & conditions**  
Power Supply System **Mains / Slave Operation**  
Mounting Method/Form **Ceiling, Wall Surface**  
Housing Material **Metal**  
Colour **White**  
Dimensions (LxWxD) **400 x 140 x 100 mm**  
Temperature Range **0 to 40°C**  
Weight **1.3 Kg**

Emergency Duration (Hours) **Mains / Central Battery Hours**  
Battery **Mains / Central Battery**  
Monitoring Equipment **EMEX test**  
Lamp **1 x 2W LED**  
Emergency Light Output (Lumens) **207**  
Average Lifespan light source (Hours) **100000 Hours**  
Light Colour/Temperature/CRI **White / 4000 / 80**  
Degree of Protection **IP65 IK10**

Type of Legend **Single or Double Sided**  
Exit Sign Viewing/Recognition Distance (m) **27**  
Nominal Voltage **220-240v AC 50/60Hz**  
Power Consumption **4.6 VA / 4.4 Watts**  
Current **Nominal: 13.59mA (mA) Inrush: 1.1A**

### Accessories

**XEN2/2DV32** Double sided Diffuser with Down+Down ISO7010 Legend  
**XEN3/6DV32** Double sided Diffuser with Left+Right ISO7010 Legend  
**XEN5/5DV32** Double sided Diffuser with Up+Up ISO7010 Legend

**XB10DV32** Double sided Diffuser with Blank+Arabic English Legend  
**XB11DV32** Double sided Diffuser with Arabic English+Arabic English Legend  
**XB23DV32** Double sided Diffuser with Arabic English Left+Arabic English Right Legend  
**XB50DV32** Double sided Diffuser with Blank+Arabic English Up Legend  
**XB66DV32** Double sided Diffuser with Arabic English Down+Arabic English Down Legend

**BBZ** Semi recessing bezel White



**Double Sided Exit Sign**  
LTCWWA1LS1X + XEN2/2DV32

