产品认证证书

II型自愿认证

证书编号：CQC2018010304134049

发证日期：2022年02月15日

有效期至：2032年02月15日

委托人名称及注册地址	ABB France 11 Rue d' Arsonval 69680, Chassieu, FRANCE
制造商名称及注册地址	ABB France 11 Rue d' Arsonval 69680, Chassieu, FRANCE
生产企业名称及生产地址	ABB Bulgaria EOOD – Rakovski branch BULGARIA, 4142 Village of Stryama, Region of Plovdiv, Municipality of Rakovski, Rakovski Industrial Zone, 14 Industrial Road 1, nr,14-18
产品名称和系列、规格、型号	交流接触器 AF45, AF50, AF63, AF75；详见附件
产品标准和技术要求	GB/T 14048.4-2020
认证模式	产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC12-000001-2020 认证规则的要求，特发此证。

本证书为变更证书，证书首次颁发日期：2020 年 08 月 21 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站（www.cnca.gov.cn）查验证书信息

授权签字人 陈昕　　签发 谢肇煦

CQC 中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心

C(2) 0138153

CERTIFICATE OF PRODUCT CERTIFICATION

TYPE II CQC CERTIFICATION

CERTIFICATE NO.: CQC2018010304134049

Valid from: Feb.15,2022

Valid until: Feb.15,2032

NAME AND REGISTERED ADDRESS OF THE APPLICANT	ABB France 11 Rue d' Arsonval 69680, Chassieu, FRANCE
NAME AND REGISTERED ADDRESS OF THE MANUFACTURER	ABB France 11 Rue d' Arsonval 69680, Chassieu, FRANCE
NAME AND LOCATION OF THE FACTORY	ABB Bulgaria EOOD – Rakovski branch BULGARIA, 4142 Village of Stryama, Region of Plovdiv, Municipality of Rakovski, Rakovski Industrial Zone, 14 Industrial Road 1, nr,14-18
PRODUCT NAME, MODEL AND SPECIFICATION	AC Contactor AF45, AF50, AF63, AF75 ; See the appendix
THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS	GB/T 14048.4-2020
TYPE OF CERTIFICATION SCHEMES	Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020.

Date of original issued: Aug.21,2020

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn

SIGN BY 陈昕

SIGNATURE 谢肇煦

CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心 CHINA QUALITY CERTIFICATION CENTRE

http://www.cqc.com.cn Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China Tel: +86 10 83886666

C(2) 0138153

产品认证证书

II型自愿认证

证书编号：CQC2018010304134049

本证书及附件应同时使用，信息查验说明见证书页

纸号：

AF45, AF50, AF63, AF75
Uimp：8kV;
Ui：1000V;
Ith：AF45, AF50：100A， AF63, AF75：125A;
AF45-22/40：
AC-1：Ue/Ie：690V/70A;
AC-3,AC-3e,AC-4：Ue/Ie：220-230-240V/40A，380-400/415/440V/37A，
500V/33A,690V/25A;
AF50-30：
AC-1：Ue/Ie：690V/100A;
AC-3,AC-3e,AC-4：Ue/Ie：220-230-240V/53A，380-400/415V/50A，
440/500V/45A,690V/35A;
AC-8a：Ue/Ie：400V/63A;
AF50-40：
AC-1：Ue/Ie：690V/100A;
AC-3,AC-3e,AC-4：Ue/Ie：220-230-240V/53A，380-400/415V/50A，
440/500V/45A,690V/35A;
AF63:
AC-1：Ue/Ie：690V/115A;
AC-3,AC-3e,AC-4：Ue/Ie：220-230-240/380-400/415/440V/65A，
500V/55A,690V/43A;
AC-8a：Ue/Ie：400V/85A;
AF75-30:
AC-1：Ue/Ie：690V/125A;
AC-3,AC-3e,AC-4：Ue/Ie：220-230-240/380-400/415V/75A，
440V/70A,500V/65A,690V/46A;
AC-8a：Ue/Ie：400V/95A;
AF75-22/40:

中国质量认证中心

产品认证证书

II型自愿认证

证书编号：CQC2018010304134049

本证书及附件应同时使用，信息查验说明见证书页　　纸号：

AC-1：Ue/Ie：690V/125A;
AC-3,AC-3e,AC-4：Ue/Ie：220-230-240/380-400/415V/75A，
440V/70A,500V/65A,690V/46A;
极数：3P,4P;
Us：20-60VDC,48-130VAC/DC 50/60Hz，100-250VAC/DC 50/60Hz;
外壳防护等级：IP10;
配用的辅助触头:（外置）
CAL5：（CQC2013010304604041）;
1NO1NC;
Ith:16A;
AC-15:Ue/Ie: 24~127V/6A, 220~240V/4A, 380~440V/3A, 500~690V/2A;
DC-13:Ue/Ie: 24V/6A, 48V/2.8A, 72V/1A, 110~125V/0.55A, 220~250V/0.3A;

中国质量认证中心

产品认证证书
II型自愿认证

证书编号：CQC2018010304134049

本证书及附件应同时使用，信息查验说明见证书页　　纸号：

型号解释：

Example 例如: AF75-30-11RT-70					
AF	75	-30	-11	RT	-70
I	II	III	IV	V	VI

I – Name of series 系列名称

AF series AF 系列

II – Size of contactor 大小

45, 50, 63, 75

III – Number of main contacts 主触头数量

22 = 2 NO- and 2 NC-contacts

30 = 3 NO- and 0 NC-contacts

40 = 4 NO- and 0 NC-contacts

IV - Number of auxiliary contacts 辅助触头数量

00 = No auxiliary pole provided.

11 = 1 NO- and 1 NC-contacts, side mounting CAL5-11 (Only on the 3 pole)

V - Connection type 端子接线方式

Blank = Screw type connection 空白 = 螺钉接线

RT = Ring Tongue connection 环形端子接线

VI - Coil code 线圈代码

中国质量认证中心

产品认证证书

II型自愿认证

证书编号：CQC2018010304134049

本证书及附件应同时使用，信息查验说明见证书页

纸号：

Control voltage		Coil code
50/60Hz	DC	
-	20-60V	72
48-130V	48-130V	69
100-250V	100-250V	70

中国质量认证中心