



## RL-230HF/LED

Slave 1 watt, 230 Volt surface mount/recess led renovation module, series Optilux

### Product Information

Type	RL-230HF/LED
Catalog number	11122106
Category_	Escape route signalisation
GTIN	08713812745503
GID	7TCA091130R0016
Serie	Optilux
Warranty (Year)	5
Other	This replacemend / renovation LED kit is placed in the existing first fix of the original luminaire. The Optilux led is only suited for use as a escape route signalisation luminaire!



### Characteristics

Power supply system	Central
Continuous operation	Yes
Mounting Method	Renovation
Mounting form	Renovation
Material housing	Plastic
Colour housing	White / aluminium
Material cover	Plastic, transparent
Material	Polycarbonate
Colour	White / aluminium
Length (mm)	364
Width (mm)	167
Height/depth (mm)	78
Nominal voltage (V)	230
Voltage type	AC/DC
Monitoring equipment	None
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	1
Number of lamps	1
Average lifespan light source (hours)	100.000
Colour of light	White
Colour temperature (K)	6350
CRI	73
Protection class	I
Degree of protection (IP)	20
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Only single-sided
Labelling type	Foil / acrylic plate
Recognition distance (m)	25
Circuit	Other
Power consumption maintained mode (W)	3,1
Apparent power consumption maintained mode (VA)	6,8
Nominal current (mA)	29,6

Inrush Current (A - 0.1ms)	27
Powerfactor	0,46
Temperature range (°C)	0 ~ +35

#### **Article Details**

Product class	Emergency luminaire
E-code	EC001957
Discount group	30405
Harmonized code	9405408440
GLN	8713812000008

#### **Ordering information**

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

#### **Supply Information**

Weight (kg)	0,882
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	426 x 188 x 111