

PRODUCT SPECIFICATION

IND1LS5DSLTC

Indulux 230v AC IP68 EMEX Test Surface

Catalogue Number **IND1LS5DSLTC**

GID **7TCA091720R0177**

Warranty **4 Year/s Refer to ABB warranty terms & conditions**

Power Supply System **Mains / Slave Operation**

Mounting Method/Form **Ceiling, Wall Surface**

Housing Material **316L stainless steel/plastic**

Colour **Silver/Clear**

Dimensions (LxWxD) **398 x 100 x 100 mm**

Temperature Range **-25 to +40°C**

Weight **1.4 Kg**

Emergency Duration (Hours) **Mains / Central Battery Hours**

Battery **Mains / Central Battery**

Monitoring Equipment **EMEX test**

Lamp **2 x 10W LED**

Emergency Light Output (Lumens) **800**

Average Lifespan light source (Hours) **60000 Hours**

Light Colour/Temperature/CRI **White / 6000 / 80**

Degree of Protection **IP68 IK10**

Type of Legend **Single or Double Sided**

Exit Sign Viewing/Recognition Distance (m) **17**

Nominal Voltage **220-240v AC 50/60Hz**

Power Consumption **7 VA / 6.5 Watts**

Current **Nominal: 30mA (mA) Inrush: 2A**

Accessories

102601K Cable Entry Cover kit

102702K



Configurable pictograms included



Luminaire

