

PRODUCT SPECIFICATION

WWA1LS11

Weatherforce 110-230V AC/DC PRIS IP65 Surface

Catalogue Number **WWA1LS11**
GID **7TCA091130R0550**
Warranty **3 Year/s Refer to ABB warranty terms & conditions**
Power Supply System **Mains / Slave Operation**
Mounting Method/Form **Ceiling, Wall Surface**
Housing Material **Metal/plastic**
Colour **White**
Dimensions (LxWxD) **400 x 140 x 100 mm**
Temperature Range **0 to 40°C**
Weight **1.54 Kg**

Emergency Duration (Hours) **Mains / Central Battery Hours**
Battery **Mains / Central Battery**
Monitoring Equipment **None**
Lamp **1 x 2W LED**
Emergency Light Output (Lumens) **207**
Average Lifespan light source (Hours) **100000 Hours**
Light Colour/Temperature/CRI **White / 4000 / 80**
Degree of Protection **IP65 IK10**

Type of Legend **Single Sided**
Exit Sign Viewing/Recognition Distance (m) **24**
Nominal Voltage **110-230v AC/DC 0-60Hz**
Power Consumption **3.4 VA / 3.2 Watts**
Current **Nominal: 13.59mA (mA) Inrush: 1.1A**

Accessories

- RSEN2120** Down ISO7010 Legend
- RSEN3120** Left ISO7010 Legend
- RSEN6120** Right ISO7010 Legend
- RSEN5120** Up ISO7010 Legend
- RSEN120** ISO7010 Legend Separate Arrow for Up, Down, Left or Right installation
- RSB1B** Arabic English Legend
- BBZ** Semi recessing bezel White



Exit Sign
WWA1LS11 + RSEN5120



Bulkhead
WWA1LS11

