



# 中国国家强制性产品认证证书

证书编号：2024010303658960

认证委托人名称及地址

ABB AG  
Kallstadter Str. 1 68309 Mannheim Germany

生产者名称及地址

ABB AG - STOTZ-KONTAKT  
Eppelheimer Str. 82 DE-69123 Heidelberg

生产企业名称及地址

ABB AG - STOTZ-KONTAKT  
Eppelheimer Str. 82 DE-69123 Heidelberg

产品名称和系列、型号、规格  
接触器式继电器及其配用辅助触头

K6,KC6,CA6,CAF6:

Ui:690V;Uimp:6kV;AC-15:Ue/Ie:240V/4A,440V/3A,500V/2A;DC-13:Ue/Ie:24V/2.5A,125V/0.7A,250V/0.4A;Ith:6A; Us:24V,42V,48V,110-127V,220-240V,380-415V

40-450Hz,6V,12V,20V,24V,42V,48V,60V,110-125V,220-240V DC;外壳防护等级:IP20;

注:CA6,CAF6 为配用辅助触头; 型号解释见附页

产品标准和技术要求

GB/T 14048.5-2017

上述产品符合《强制性产品认证实施规则 低压电器 低压元器件》  
(CNCA-C03-02:2024) 的要求, 特发此证。

发证日期: 2026年05月15日 有效期至: 2029年07月16日

本证书为变更证书, 证书首次颁发日期: 2024年07月17日  
证书信息和有效性可扫描下方二维码或登录发证机构网站查验,  
也可在认监委网站 (www.cnca.gov.cn) 查询。



签发:

刘江



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司





# 中国国家强制性产品认证证书

证书编号：2024010303658960

证书附页：第 1 页 共 2 页

型号解释：

Full type 型号		KC6-22Z-F-1.4-01									
		KC6	—	22	Z	—	F	—	1.4	—	01
Position	Product 产品	√	√	√	√	√	√	√	√		
位置	package label 包装标签	√	√	√	√	√	√	√	√	√	√

1: 产品型号, K6: 交流线圈  
KC6: 直流线圈

2: 触点类型: 第一位常开触点数量, 第二位常闭触点数量  
40: 4NO, 31: 3NO+1NC, 22: 2NO+2NC

3: 接线端子标识代号: 40E, 22Z, 31Z

4: 接线端子类型: 空白: 螺钉端子 P: 焊接插针端子 F: 插片端子

5: 线圈类型: 空白: 标准产品  
数字: 低功耗线圈, 可由 PLC 信号直接驱动, 数字为线圈吸持功耗值

本页为证书附页, 应与证书主页同时使用。



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司



# 中国国家强制性产品认证证书

证书编号：2024010303658960

证书附页：第 2 页 共 2 页

6: 线圈代号:

Control Voltage ac (40-450Hz)	代码 □...□	Control Voltage dc	代码 □...□
24 V	0..1	6 V	0..6
42 V	0..2	12 V	0..7
48 V	0..3	20 V	0..9
110-127 V	8..4	24 V	0..1
220-240 V	8..0	42 V	0..2
380-415 V	8..5	48 V	1..6
		60 V	1..6
		110-125 V	1..6
		220-240 V	0..5

CA6 - 11 - K - P  
1 2 3 4

1: 产品型号: CA6: 侧装, CAF6: 前装

2: 触点类型: 第一位常开触点数量, 第二位常闭触点数量

CA6: 11: 1NO+1NC

CAF6: 11: 1NO+1NC 20: 2NO 02: 2NC

3: 接线端子标识代号: 接触器或继电器配合代号

K: K6..KC6

E: B(C)6-40-00,B(C)7-40-00

M: B(C)6-30-10,B(C)7-30-10

N: B(C)6-30-01,B(C)7-30-01

4: 接线端子类型: 空白: 螺钉端子 P: 焊接插针端子 F: 插片端子

本页为证书附页, 应与证书主页同时使用。



中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司



# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，  
不得单独使用  
This translated document  
does not have legal validity and  
cannot be used in isolation

**CERTIFICATE NO.:** 2024010303658960

**NAME AND ADDRESS OF THE APPLICANT**

ABB AG  
Kallstadter Str. 1 68309 Mannheim Germany

**NAME AND ADDRESS OF THE MANUFACTURER**

ABB AG – STOTZ-KONTAKT  
Eppelheimer Str. 82 DE-69123 Heidelberg

**NAME AND LOCATION OF THE FACTORY**

ABB AG – STOTZ-KONTAKT  
Eppelheimer Str. 82 DE-69123 Heidelberg

**PRODUCT NAME,MODEL AND SPECIFICATION**

Contactor relay and its auxiliary contacts

K6,KC6,CA6,CAF6 :

Ui:690V;Uimp:6kV;AC-15:Ue/Ie:240V/4A,440V/3A,500V/2A;DC-13:Ue/Ie:24V/2.5A,125V/0.7A,250V/0.4A;Ith:6A ;  
Us:24V,42V,48V,110-127V,220-240V,380-415V 40-450Hz,6V,12V,20V,24V,42V,48V,60V,110-125V,220-240V DC;IP20;  
注:CA6,CAF6 Auxiliary Contact

**STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS**

GB/T 14048.5-2017

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

**Valid from:** May.15,2026

**Valid until:** Jul.16,2029

Date of original issued: Jul.17,2024

The certificate information and validity could be checked by scanning the QR code below or logging in to the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，  
不得单独使用  
This translated document  
does not have legal validity and  
cannot be used in isolation

CERTIFICATE NO. : 2024010303658960

Appendix: Page 1 of 2

Full type 型号		KC6-22Z-F-1.4-01									
		KC6	—	22	Z	—	F	—	1.4	—	01
Position	Product 产品	1		2	3		4		5		6
位置	package label 包装标签	√	√	√	√	√	√	√	√	√	√

1: 产品型号, K6: 交流线圈  
KC6: 直流线圈

2: 触点类型: 第一位常开触点数量, 第二位常闭触点数量  
40: 4NO, 31: 3NO+1NC, 22: 2NO+2NC

3: 接线端子标识代号: 40E, 22Z, 31Z

4: 接线端子类型: 空白: 螺钉端子 P: 焊接插针端子 F: 插片端子

5: 线圈类型: 空白: 标准产品  
数字: 低功耗线圈, 可由 PLC 信号直接驱动, 数字为线圈吸持功耗值

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.



# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，  
不得单独使用  
This translated document  
does not have legal validity and  
cannot be used in isolation

CERTIFICATE NO. : 2024010303658960

Appendix: Page 2 of 2

6: 线圈代号:

Control Voltage ac (40-450Hz)	代码 □...□	Control Voltage dc	代码 □...□
24 V	0..1	6 V	0..6
42 V	0..2	12 V	0..7
48 V	0..3	20 V	0..9
110-127 V	8..4	24 V	0..1
220-240 V	8..0	42 V	0..2
380-415 V	8..5	48 V	1..6
		60 V	1..6
		110-125 V	1..6
		220-240 V	0..5

CA6 - 11 K - P  
1 2 3 4

1: 产品型号: CA6: 侧装, CAF6: 前装

2: 触点类型: 第一位常开触点数量, 第二位常闭触点数量

CA6: 11: 1NO+1NC

CAF6: 11: 1NO+1NC 20: 2NO 02: 2NC

3: 接线端子标识代号: 接触器或继电器配合代号

K: K6..KC6

E: B(C)6-40-00,B(C)7-40-00

M: B(C)6-30-10,B(C)7-30-10

N: B(C)6-30-01,B(C)7-30-01

4: 接线端子类型: 空白: 螺钉端子 P: 焊接插针端子 F: 插片端子

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.