

PRODUCT SPECIFICATION

VVE8LS1X

Navigator Compact 110-230V AC/DC 32M IP20 Wall Surface

Catalogue Number **VVE8LS1X**
GID **7TCA091130R0548**
Warranty **3 Year/s Refer to ABB warranty terms & conditions**
Power Supply System **Mains / Slave Operation**
Mounting Method/Form **Wall Surface**
Housing Material **Metal**
Colour **White**
Dimensions (LxWxD) **358 x 185 x 71 mm**
Temperature Range **0 to 40°C**
Weight **1.69 Kg**

Emergency Duration (Hours) **Central Battery**
Battery **Central Battery**
Monitoring Equipment **None**
Lamp **1 x 1W LED**
Emergency Light Output (Lumens) **Not Applicable**
Average Lifespan light source (Hours) **100000 Hours**
Light Colour/Temperature/CRI **White / 4000 / 80**
Degree of Protection **IP20**

Type of Legend **Single Sided**
Exit Sign Viewing/Recognition Distance (m) **32**
Nominal Voltage **110-230v AC/DC 0-60Hz**
Power Consumption **3.4 VA / 2.1 Watts**
Current **Nominal: 57mA (mA) Inrush: 1.1A**

Accessories

XEN2V31 Down ISO7010 Legend
XEN3V31 Left ISO7010 Legend
XEN6V31 Right ISO7010 Legend
XEN5V31 Up ISO7010 Legend
XB01V31 Arabic English Legend

VEBACK Rear Trim Plate for Ceiling Mount



Exit Sign
VVE8LS1X + XEN2V31

