

产品认证证书

II型自愿认证

证书编号: CQC2015010307760141

发证日期: 2021年08月05日

有效期至: 2031年08月05日

委托人名称及注册地址 ABB Stotz-Kontakt GmbH
Eppelheimer Strasse 82 69123 Heidelberg Germany

制造商名称及注册地址 ABB Stotz-Kontakt GmbH
Eppelheimer Strasse 82 69123 Heidelberg Germany

生产企业名称及生产地址 A B B 新会低压开关有限公司
广东省江门市新会区今古洲工业开发区

产品名称和系列、规格、型号 电动机保护用断路器
MS165, MO165; 规格参数详见附件

产品标准和技术要求 GB/T 14048.2-2020;GB/T 14048.4-2020

认证模式 产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC12-000001-2020 认证规则的要求, 特发此证。

本证书为变更证书, 证书首次颁发日期: 2020年08月14日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



授权签字人

签发

刘江

谢肇煦

中国质量认证中心



<http://www.cqc.com.cn>

中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666

C(2) 0089801

CERTIFICATE OF PRODUCT CERTIFICATION

TYPE II CQC CERTIFICATION

CERTIFICATE NO.: CQC2015010307760141

Valid from: Aug.05,2021

Valid until: Aug.05,2031

NAME AND REGISTERED ADDRESS OF THE APPLICANT	ABB Stotz-Kontakt GmbH Eppelheimer Strasse 82 69123 Heidelberg Germany
NAME AND REGISTERED ADDRESS OF THE MANUFACTURER	ABB Stotz-Kontakt GmbH Eppelheimer Strasse 82 69123 Heidelberg Germany
NAME AND LOCATION OF THE FACTORY	ABB Xinhui Low Voltage Switchgear Co., Ltd. Jinguzhou Industrial Development Zone, Xinhui District, Jiangmen City, Guangdong Province, P.R.China
PRODUCT NAME, MODEL AND SPECIFICATION	Motor protection circuit breaker MS165, MO165; See the Appendix
THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS	GB/T 14048.2-2020;GB/T 14048.4-2020
TYPE OF CERTIFICATION SCHEMES	Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020.

Date of original issued: Aug.14,2020

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGN BY

SIGNATURE



CHINA QUALITY CERTIFICATION CENTRE



<http://www.cqc.com.cn>

Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P.R. China

Tel: +86 10 83886666

C(2) 0089801

产品认证证书

II型自愿认证

证书编号: CQC2015010307760141

第 1 页 共 3 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 89801

上报参数:

MS165, MO165

Uimp: 8kV;

Ui: 1000V;

Ue: AC400V, AC690V;

In: 10-16A, 14-20A, 18-25A, 23-32A, 30-42A, 40-54A, 52-65A, 62-73A, 70-80A(MS165);

16A, 20A, 25A, 32A, 42A, 54A, 65, 73, 80A(MO165);

过电流脱扣器类型:热磁式(MS165), 电磁式(MO165);

AC400V:

Ics=Icu=100kA(MS165-16, MO165-16, MS165-16B, MO165-16B, MS165-20, MO165-20, MS165-20B, MO165-20B, MS165-25, MO165-25, MS165-25B, MO165-25B, MS165-32, MO165-32, MS165-32B, MO165-32B);

Ics=Icu=50kA(MS165-42, MO165-42, MS165-42B, MO165-42B);

Ics=30kA, Icu=50kA(MS165-54, MO165-54, MS165-54B, MO165-54B, MS165-65, MO165-65, MS165-65B, MO165-65B);

Ics=Icu=30kA(MS165-73, MO165-73, MS165-80, MO165-80);

AC690V:

Ics=Icu=10kA(MS165-16, MO165-16, MS165-16B, MO165-16B, MS165-20, MO165-20, MS165-20B, MO165-20B, MS165-25, MO165-25, MS165-25B, MO165-25B, MS165-32, MO165-32, MS165-32B, MO165-32B, MS165-42, MO165-42, MS165-42B, MO165-42B);

Ics=6kA, Icu=8kA(MS165-54, MO165-54, MS165-54B, MO165-54B, MS165-65, MO165-65, MS165-65B, MO165-65B, MS165-73, MO165-73, MS165-80, MO165-80);

选择性类别: A;

使用类别: AC-3, AC-3e;

适用频率: 50/60Hz;

适用于隔离;

脱扣级别:10;

极数: 3P;



中国质量认证中心

