



EVA-COP-32/FLX

Slave 4 watt, 230 Volt aluminium surface 32 meter led luminaire, including control module, series Evago. The luminaire is including the pictogram PP 320/51 (escape route straight forward) + green pictogram (PP 320/50)

Product Information

Type	EVA-COP-32/FLX
Catalog number	4510257353
Category_	Escape route signalisation
GTIN	08713812762623
GID	7TCA091140R0359
Serie	Evago
Warranty (Year)	5



Characteristics

Power supply system	Central
Continuous operation	Yes
Mounting Method	Ceiling
Mounting form	Surface
Material housing	Aluminium
Colour housing	Aluminium
Material	Aluminium
Colour	Aluminium
Length (mm)	335
Width (mm)	66
Height/depth (mm)	222
Nominal voltage (V)	230
Voltage type	AC/DC
Monitoring equipment	Safety module for monitoring
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	4
Number of lamps	1
Average lifespan light source (hours)	100.000
Colour of light	White
Colour temperature (K)	5000
CRI	80
Protection class	II
Degree of protection (IP)	40
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Single / double-sided
Labelling type	Insert sheet/plate
Recognition distance (m)	32
Circuit	Other
Power consumption maintained mode (W)	6,5
Apparent power consumption maintained mode (VA)	7,1
Nominal current (mA)	31
Powerfactor	> 0,9
Temperature range (°C)	0 ~ +35

Article Details

Product class	Emergency luminaire
E-code	EC001957
Discount group	30406
Harmonized code	9405408440
GLN	8713812000008

Ordering information

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

Supply Information

Weight (kg)	1,398
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	400 x 250 x 88