

FOR THXXXXJR CATALOGS ONLY

WINDOW FOR THXXXXJW CATALOGS




FIG. 1





FIG. 2



DIMENSION TABLE

| GCAT NO. | FIG. | A | B | C | D | E | F | G | H | I |
|---|------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| THN2263JDC | 1 | 25.36 | 13.42 | 14.04 | 13.12 | 25.08 | 26.28 | 10.50 | 10.12 | - |
| TH3223J/TH4323J/THN3363J/TH3363J/THN3363JCL/TH2263JDC | 1 | 25.36 | 13.42 | 14.04 | 13.14 | 25.08 | 26.28 | 10.50 | 10.12 | - |
| THN3363JW/TH3363JW | 2 | 25.36 | 13.42 | 14.04 | 13.14 | 25.08 | 26.28 | 10.50 | 10.12 | - |
| TH3363JR | 1 | 25.36 | 13.42 | 14.04 | 13.14 | 25.08 | 26.28 | 10.50 | 10.12 | 13.59 |
| TH3364J/TH4324J/TH3224J/THN3364J | 1 | 35.14 | 14.45 | 15.07 | 14.14 | 34.83 | 36.06 | 11.50 | 10.12 | - |
| TH3224JW/TH4324JW | 2 | 35.14 | 14.45 | 15.07 | 14.14 | 34.83 | 36.06 | 11.50 | 10.12 | - |
| THN3364JW/TH3364JW | 2 | 35.14 | 14.45 | 15.07 | 14.14 | 34.83 | 36.06 | 11.50 | 10.12 | - |
| TH3364JR | 1 | 35.14 | 14.45 | 15.07 | 14.14 | 34.83 | 36.06 | 11.50 | 10.12 | 14.59 |
| TH3223JW/TH4323JW | 2 | 25.36 | 13.42 | 14.04 | 13.12 | 25.08 | 26.28 | 10.50 | 10.12 | - |

NOTE:
 1. ALL DIMENSIONS ARE IN INCHES.
 2. ALL DIMENSIONS HAVE ±0.125 TOLERANCE.



Industrial Solutions

by ABB

OUTLINE DRAWING-HEAVY DUTY 100 & 200A
 NEMA-12 & 12/3R, WITH & WITHOUT VIEWING WINDOW

| | |
|-------------|--------|
| THIRD ANGLE | SHEET# |
| | 1 of 1 |

| | | |
|---------------|-------|-----|
| DWG NO. | DATE | REV |
| 10103091SH120 | 10/19 | 06 |