

SH200 M - MCBs, C Characteristics - 10 kA



Description	Ordering Code	Current Rating (A)	M.R.P.(₹)	Pack Unit (Pc)
Single pole				
SH201M-C 0.5	2CDS271011R0984	0.5	280	12
SH201M-C 1	2CDS271011R0014	1	280	12
SH201M-C 1.6	2CDS271011R0974	1.6	280	12
SH201M-C 2	2CDS271011R0024 ■	2	280	12
SH201M-C 3	2CDS271011R0034	3	280	12
SH201M-C 4	2CDS271011R0044	4	280	12
SH201M-C 6	2CDS271011R0064 ■	6	188	12
SH201M-C 8	2CDS271011R0084	8	188	12
SH201M-C 10	2CDS271011R0104 ■	10	188	12
SH201M-C 16	2CDS271011R0164 ■	16	188	12
SH201M-C 20	2CDS271011R0204 ■	20	188	12
SH201M-C 25	2CDS271011R0254 ■	25	188	12
SH201M-C 32	2CDS271011R0324 ■	32	188	12
SH201M-C 40	2CDS271011R0404	40	385	12
SH201M-C 50	2CDS271011R0504	50	392	12
SH201M-C 63	2CDS271011R0634 ■	63	392	12
Single Pole & Neutral				
SH201M-C 0.5 NA	2CDS271113R0984	0.5	765	6
SH201M-C 1 NA	2CDS271113R0014	1	765	6
SH201M-C 1.6 NA	2CDS271113R0974	1.6	765	6
SH201M-C 2 NA	2CDS271113R0024	2	765	6
SH201M-C 3 NA	2CDS271113R0034	3	765	6
SH201M-C 4 NA	2CDS271113R0044	4	765	6
SH201M-C 6 NA	2CDS271113R0064	6	545	6
SH201M-C 8 NA	2CDS271113R0084	8	545	6
SH201M-C 10 NA	2CDS271113R0104	10	545	6
SH201M-C 16 NA	2CDS271113R0164	16	545	6
SH201M-C 20 NA	2CDS271113R0204	20	545	6
SH201M-C 25 NA	2CDS271113R0254	25	545	6
SH201M-C 32 NA	2CDS271113R0324	32	545	6
SH201M-C 40 NA	2CDS271113R0404	40	870	6
SH201M-C 50 NA	2CDS271113R0504	50	880	6
SH201M-C 63 NA	2CDS271113R0634	63	880	6
Double Pole				
SH202M-C 0.5	2CDS272011R0984	0.5	770	6
SH202M-C 1	2CDS272011R0014	1	770	6
SH202M-C 1.6	2CDS272011R0974	1.6	770	6
SH202M-C 2	2CDS272011R0024 ■	2	770	6
SH202M-C 3	2CDS272011R0034	3	770	6
SH202M-C 4	2CDS272011R0044 ■	4	770	6
SH202M-C 6	2CDS272011R0064 ■	6	548	6
SH202M-C 8	2CDS272011R0084	8	548	6
SH202M-C 10	2CDS272011R0104 ■	10	548	6
SH202M-C 16	2CDS272011R0164 ■	16	548	6
SH202M-C 20	2CDS272011R0204 ■	20	548	6
SH202M-C 25	2CDS272011R0254 ■	25	548	6
SH202M-C 32	2CDS272011R0324 ■	32	548	6
SH202M-C 40	2CDS272011R0404 ■	40	880	6
SH202M-C 50	2CDS272011R0504	50	890	6
SH202M-C 63	2CDS272011R0634	63	890	6

■ Stock items

6 MCB | DIN Rail Products

SH200 M - MCBs, C Characteristics - 10 kA



Description	Ordering Code	Current Rating (A)	M.R.P.(₹)	Pack Unit (Pc)
Triple Pole				
SH203M-C 0.5	2CDS273011R0984	0.5	1,155	4
SH203M-C 1	2CDS273011R0014	1	1,155	4
SH203M-C 1.6	2CDS273011R0974	1.6	1,155	4
SH203M-C 2	2CDS273011R0024	2	1,155	4
SH203M-C 3	2CDS273011R0034	3	1,155	4
SH203M-C 4	2CDS273011R0044	4	1,155	4
SH203M-C 6	2CDS273011R0064	6	885	4
SH203M-C 8	2CDS273011R0084	8	885	4
SH203M-C 10	2CDS273011R0104	10	885	4
SH203M-C 16	2CDS273011R0164 ■	16	885	4
SH203M-C 20	2CDS273011R0204	20	885	4
SH203M-C 25	2CDS273011R0254	25	885	4
SH203M-C 32	2CDS273011R0324 ■	32	885	4
SH203M-C 40	2CDS273011R0404	40	1,350	4
SH203M-C 50	2CDS273011R0504	50	1,365	4
SH203M-C 63	2CDS273011R0634 ■	63	1,365	4
Triple Pole & Neutral				
SH203M-C 0.5 NA	2CDS273113R0984	0.5	1,480	3
SH203M-C 1 NA	2CDS273113R0014	1	1,480	3
SH203M-C 1.6 NA	2CDS273113R0974	1.6	1,480	3
SH203M-C 2 NA	2CDS273113R0024	2	1,480	3
SH203M-C 3 NA	2CDS273113R0034	3	1,480	3
SH203M-C 4 NA	2CDS273113R0044	4	1,480	3
SH203M-C 6 NA	2CDS273113R0064	6	1,182	3
SH203M-C 8 NA	2CDS273113R0084	8	1,182	3
SH203M-C 10 NA	2CDS273113R0104	10	1,182	3
SH203M-C 16 NA	2CDS273113R0164	16	1,182	3
SH203M-C 20 NA	2CDS273113R0204	20	1,182	3
SH203M-C 25 NA	2CDS273113R0254	25	1,182	3
SH203M-C 32 NA	2CDS273113R0324 ■	32	1,182	3
SH203M-C 40 NA	2CDS273113R0404 ■	40	1,740	3
SH203M-C 50 NA	2CDS273113R0504	50	1,760	3
SH203M-C 63 NA	2CDS273113R0634 ■	63	1,760	3
Four Pole				
SH204M-C 0.5	2CDS274011R0984	0.5	1,492	3
SH204M-C 1	2CDS274011R0014	1	1,492	3
SH204M-C 1.6	2CDS274011R0974	1.6	1,492	3
SH204M-C 2	2CDS274011R0024	2	1,492	3
SH204M-C 3	2CDS274011R0034	3	1,492	3
SH204M-C 4	2CDS274011R0044	4	1,492	3
SH204M-C 6	2CDS274011R0064	6	1,185	3
SH204M-C 8	2CDS274011R0084	8	1,185	3
SH204M-C 10	2CDS274011R0104	10	1,185	3
SH204M-C 16	2CDS274011R0164	16	1,185	3
SH204M-C 20	2CDS274011R0204	20	1,185	3
SH204M-C 25	2CDS274011R0254	25	1,185	3
SH204M-C 32	2CDS274011R0324 ■	32	1,185	3
SH204M-C 40	2CDS274011R0404 ■	40	1,745	3
SH204M-C 50	2CDS274011R0504	50	1,765	3
SH204M-C 63	2CDS274011R0634 ■	63	1,765	3

■ Stock items

SH200 M - MCBs, D Characteristics - 10 kA



Description	Ordering Code	Current Rating (A)	M.R.P.(₹)	Pack Unit (Pc)
Single pole				
SH201M-D 0.5	2CDS271011R0981	0.5	315	12
SH201M-D 1	2CDS271011R0101	1	315	12
SH201M-D 1.6	2CDS271011R0971	1.6	315	12
SH201M-D 2	2CDS271011R0101	2	315	12
SH201M-D 3	2CDS271011R0031	3	315	12
SH201M-D 4	2CDS271011R0041	4	315	12
SH201M-D 6	2CDS271011R0061 ■	6	235	12
SH201M-D 8	2CDS271011R0081	8	235	12
SH201M-D 10	2CDS271011R0101 ■	10	235	12
SH201M-D 16	2CDS271011R0161 ■	16	235	12
SH201M-D 20	2CDS271011R0201 ■	20	235	12
SH201M-D 25	2CDS271011R0251 ■	25	235	12
SH201M-D 32	2CDS271011R0321 ■	32	235	12
SH201M-D 40	2CDS271011R0401	40	432	12
SH201M-D 50	2CDS271011R0501	50	438	12
SH201M-D 63	2CDS271011R0631	63	438	12
Double pole				
SH202M-D 0.5	2CDS272011R0981	0.5	862	6
SH202M-D 1	2CDS272011R0111	1	862	6
SH202M-D 1.6	2CDS272011R0971	1.6	862	6
SH202M-D 2	2CDS272011R0021	2	862	6
SH202M-D 3	2CDS272011R0031	3	862	6
SH202M-D 4	2CDS272011R0041	4	862	6
SH202M-D 6	2CDS272011R0061	6	685	6
SH202M-D 8	2CDS272011R0081	8	685	6
SH202M-D 10	2CDS272011R0101	10	685	6
SH202M-D 16	2CDS272011R0161 ■	16	685	6
SH202M-D 20	2CDS272011R0201	20	685	6
SH202M-D 25	2CDS272011R0251	25	685	6
SH202M-D 32	2CDS272011R0321 ■	32	685	6
SH202M-D 40	2CDS272011R0401 ■	40	986	6
SH202M-D 50	2CDS272011R0501	50	998	6
SH202M-D 63	2CDS272011R0631	63	998	6

■ Stock items

SH200 M - MCBs, D Characteristics - 10 kA



Product Description	Ordering Code	Current Rating (A)	M.R.P.(₹)	Pack Unit (Pc)
Triple pole				
SH203M-D 0.5	2CDS273011R0981	0.5	1,294	4
SH203M-D 1	2CDS273011R0111	1	1,294	4
SH203M-D 1.6	2CDS273011R0971	1.6	1,294	4
SH203M-D 2	2CDS273011R0021	2	1,294	4
SH203M-D 3	2CDS273011R0031	3	1,294	4
SH203M-D 4	2CDS273011R0041	4	1,294	4
SH203M-D 6	2CDS273011R0061	6	1,106	4
SH203M-D 8	2CDS273011R0081	8	1,106	4
SH203M-D 10	2CDS273011R0101	10	1,106	4
SH203M-D 16	2CDS273011R0161	16	1,106	4
SH203M-D 20	2CDS273011R0201	20	1,106	4
SH203M-D 25	2CDS273011R0251	25	1,106	4
SH203M-D 32	2CDS273011R0321	32	1,106	4
SH203M-D 40	2CDS273011R0401 ■	40	1,512	4
SH203M-D 50	2CDS273011R0501	50	1,530	4
SH203M-D 63	2CDS273011R0631 ■	63	1,530	4

Four pole				
SH204M-D 0.5	2CDS274011R0981	0.5	1,670	3
SH204M-D 1	2CDS274011R0111	1	1,670	3
SH204M-D 1.6	2CDS274011R0971	1.6	1,670	3
SH204M-D 2	2CDS274011R0021	2	1,670	3
SH204M-D 3	2CDS274011R0031	3	1,670	3
SH204M-D 4	2CDS274011R0041	4	1,670	3
SH204M-D 6	2CDS274011R0061	6	1,480	3
SH204M-D 8	2CDS274011R0081	8	1,480	3
SH204M-D 10	2CDS274011R0101	10	1,480	3
SH204M-D 16	2CDS274011R0161	16	1,480	3
SH204M-D 20	2CDS274011R0201	20	1,480	3
SH204M-D 25	2CDS274011R0251	25	1,480	3
SH204M-D 32	2CDS274011R0321	32	1,480	3
SH204M-D 40	2CDS274011R0401 ■	40	1,956	3
SH204M-D 50	2CDS274011R0501	50	1,980	3
SH204M-D 63	2CDS274011R0631 ■	63	1,980	3

■ Stock items