




- NOTES:
- 1. MAXIMUM BAUD RATE IS 9600 (RS232)
 - 2. EXTERNAL POWER REQUIRED, RECEIVER MUST BE ON AT ALL TIMES.

REVISIONS					
REV	ACTION	DRAWN	CHECKED	APPROVED	DATE
AA	L6605	TIERNEY	TIERNEY	HOLLAND	99-02-06
AB	D12508	KASTNER	KASTNER	HOLLAND	02/01/16



ASSEMBLY/QUANTITY		ITEM NO.	PART NUMBER	DESCRIPTION	REF/ZONE DESIG MATERIAL	UNIT MEAS
PARTS LIST						
DO NOT SCALE DRAWING		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: DECIMAL ANGULAR .XX ± — ± — — .XXX ± — — — BREAK ALL SHARP CORNERS AND EDGES DIMENSIONS APPLY BEFORE FINISH		PRODUCT LINE TOTALFLOW®	LEVEL 3	 TOTALFLOW Products
				DESIGN HOLLAND	DATE 99-2-6	
				DRAWN TIERNEY	99-2-6	TITLE WIRING & INTERCONNECT METRICOM RADIO IN (6613, 6614/6615) WI
				CHECKED TIERNEY	99-2-6	
				APPROVED HOLLAND	99-2-6	SCALE NONE
						SIZE B
						DOC TYPE WI
						DRAWING NO. 2018367
						REV AB
						SHEET 1 OF 2

