

# 产品认证证书

## II型自愿认证

证书编号: CQC2004010309130463

发证日期: 2021年10月09日

有效期至: 2031年10月09日

委托人名称 ABB France  
及注册地址 11 Rue d' Arsonval 69680, Chassieu, FRANCE

制造商名称 ABB 新会低压开关有限公司  
及注册地址 广东省江门市新会区今古洲工业开发区

生产企业名称 ABB 新会低压开关有限公司  
及生产地址 广东省江门市新会区今古洲工业开发区

产品名称和系列、规格、型号 接触器  
A9, A12, A16, A9D, A16D, A26D; 规格参数详见附件

产品标准和技术要求 GB/T 14048.4-2020

认证模式 产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC12-000001-2020 认证规则的要求, 特发此证。

本证书为变更证书, 证书首次颁发日期: 2020年08月14日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站(www.cnca.gov.cn) 查验证书信息



授权签字人

签发

刘江

谢肇煦



中国质量认证中心



<http://www.cqc.com.cn>

中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666

C(2) 0110794

# CERTIFICATE OF PRODUCT CERTIFICATION

## TYPE II CQC CERTIFICATION

**CERTIFICATE NO.:** CQC2004010309130463

**Valid from:** Oct.09,2021

**Valid until:** Oct.09,2031

<b>NAME AND REGISTERED ADDRESS OF THE APPLICANT</b>	ABB France 11 Rue d' Arsonval 69680, Chassieu, FRANCE
<b>NAME AND REGISTERED ADDRESS OF THE MANUFACTURER</b>	ABB Xinhui Low Voltage Switchgear Co.,Ltd. Jinguzhou Industrial Development Zone, Xinhui District, Jiangmen City, Guangdong Province, P.R.China
<b>NAME AND LOCATION OF THE FACTORY</b>	ABB Xinhui Low Voltage Switchgear Co.,Ltd. Jinguzhou Industrial Development Zone Xinhui Region,Jiangmen City, Guangdong Province, P.R.China
<b>PRODUCT NAME, MODEL AND SPECIFICATION</b>	Contactors A9, A12, A16, A9D, A16D, A26D; See the Appendix
<b>THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS</b>	GB/T 14048.4-2020
<b>TYPE OF CERTIFICATION SCHEMES</b>	Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020.

Date of original issued: Aug.14,2020

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: [www.cnca.gov.cn](http://www.cnca.gov.cn)



SIGN BY

SIGNATURE



CHINA QUALITY CERTIFICATION CENTRE



<http://www.cqc.com.cn>

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

Tel: +86 10 83886666

C(2) 0110794

# 产品认证证书

## II型自愿认证

证书编号: CQC2004010309130463

第1页 共3页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 110794

上报参数:

A9, A12, A16, A9D, A16D, A26D

A9:

Ui:1000V;

Uimp:8kV;

Ue/le:220/230/240/380/400/415/440/500V/9A, 690V/7A(AC-3);

Ue/le:400V/12A(AC-8a);

Ue/le:690V/25A(AC-1);

Ith:26A;

A12:

Ui:1000V;

Uimp:8kV;

Ue/le:220/230/240/380/400/415/440/500V/12A, 690V/9A(AC-3);

Ue/le:400V/16A(AC-8a);

Ue/le:690V/27A(AC-1);

Ith:28A;

A16:

Ui:1000V;

Uimp:8kV;

Ue/le:220/230/240/380/400/415/17A,440V/16A,500V/14A,690V/10A(AC-3);

Ue/le:400V/22A(AC-8a);

Ue/le:690V/30A(AC-1);

Ith:30A;

A9D:

Ui:690V;

Uimp:8kV;

Ue/le:220/230/240/380/400V/9A,440V/9A(AC-3);

Ue/le:400V/9A(AC-8a);



中国质量认证中心



# 产品认证证书

## II型自愿认证

证书编号: CQC2004010309130463

第2页 共3页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 110794

Ue/Ie:690V/22A(AC-3);  
Ith:24A;  
A16D:  
Ui:690V;  
Uimp:8kV;  
Ue/Ie:220/230/240/380/400V/16A,440V/16A(AC-3);  
Ue/Ie:400V/16A(AC-8a);  
Ue/Ie:690V/27A(AC-1);  
Ith:28A;  
A26D:  
Ui:690V;  
Uimp:8kV;  
Ue/Ie:220/230/240/380/400V/16A,440V/16A(AC-3);  
Ue/Ie:400V/16A(AC-8a);  
Ue/Ie:690V/27A(AC-1);  
Ith:28A;  
Us: A9, A12, A16:  
24V 50Hz/24V 60Hz, 42V 50Hz/42V 60Hz,  
48V 50Hz/48V 60Hz, 110V 50Hz/110-120V 60Hz,  
190V 50Hz/220V 60Hz, 220-230V 50Hz/230-240 60Hz,  
230-240V 50Hz/240-260V 60Hz,  
380-400V 50Hz/400-415 60Hz,  
400-415 V 50Hz/415-440V 60Hz;  
A9D, A26D: 24V 50Hz/24V 60Hz, 220-230V 50Hz/230-240 60Hz;  
A16D: 24V 50Hz/24V 60Hz;  
极数: 3P,4P(A9, A12, A16);  
外壳防护等级:IP20;  
配用的辅助触头 (本体):



中国质量认证中心



# 产品认证证书

## II型自愿认证

证书编号: CQC2004010309130463

第 3 页 共 3 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 110794

1NO,1NC;


Ith:16A;

AC-15:Ue/Ie:24-127V/6A, 220-240V/4A,380-440V/3A,500V/2A,690V/2A;

DC-13:Ue/Ie:24V/6A,48V/2.8A,72V/2A,125V/1.1A,250V/0.55A

型号解释:

A 16 D 3 0-1 0



中国质量认证中心

