

PRODUCT SPECIFICATION

DLSTF3LS60

Aqualux Freez-Lite Self-Contained IP65 DALI Test Surface

Catalogue Number **DLSTF3LS60**
 GID **7TCA091180R0375**
 Warranty **3 Year/s Refer to ABB warranty terms & conditions**
 Power Supply System **Self-Contained (individual battery)**
 Mounting Method/Form **Ceiling, Wall Surface**
 Housing Material **Aluminium/Plastic**
 Colour **White/Silver**
 Dimensions (LxWxD) **381 x 170 x 75 mm**
 Temperature Range **-25 to +30°C**
 Weight **1.7 Kg**

Emergency Duration (Hours) **3 Hours**
 Battery **NiCd**
 Monitoring Equipment **DALI test**
 Lamp **1 x 3W LED**
 Emergency Light Output (Lumens) **119**
 Average Lifespan light source (Hours) **50000 Hours**
 Light Colour/Temperature/CRI **White / 6500 / 73**
 Degree of Protection **IP65 IK10**

Type of Legend **Single Sided (Order separate)**
 Exit Sign Viewing/Recognition Distance (m) **25**
 Nominal Voltage **220-240v AC 50Hz**
 Power Consumption **9.9 VA / 5.1 Watts**
 Current **Nominal: 42.5mA (mA) Inrush: 18A**

Accessories

XEN2W Down ISO7010 Legend for Backlit Exit Sign
XEN3W Left ISO7010 Legend for Backlit Exit Sign
XEN6W Right ISO7010 Legend for Backlit Exit Sign
XEN5W Up ISO7010 Legend for Backlit Exit Sign
XLF802W Fire Extinguisher Legend for Backlit Exit Sign
XLF803W Hose Reel Legend for Backlit Exit Sign

OW/BCM Ceiling Bracket for Vertical Mount
OW/BWA Wall Bracket for Angled Mount
OW/BWM Cantilever Bracket for End to Wall Mount
OW/BCR Recessing Kit
OW/DSC Blank double sided diffuser for Edgelite Exit Sign

RSEN2W Down ISO7010 Legend for Edgelit Exit Sign (Single Sided)
RSEN3W Left ISO7010 Legend for Edgelit Exit Sign (Single Sided)
RSEN6W Right ISO7010 Legend for Edgelit Exit Sign (Single Sided)
RSEN5W Up ISO7010 Legend for Edgelit Exit Sign (Single Sided)
RSEN3W/RSEN6W Left+Right ISO7010 Legend for Edgelit Exit Sign (Double Sided)



Edgelit Exit Sign
DLSTF3LS60 + RSEN5W + OW/DSC



Backlit Exit Sign
DLSTF3LS60 + XEN5W



Bulkhead
DLSTF3LS60

