



中国国家强制性产品认证证书

证书编号：2024010302658037

认证委托人名称及地址

ABB Oy

Muottitie 2A FI-65320 VAASA, Finland

生产者名称及地址

ABB Oy

Muottitie 2A FI-65320 VAASA, Finland

生产企业名称及地址

ABB Oy

Muottitie 2A FI-65320 VAASA, Finland

产品名称和系列、型号、规格

隔离开关

OT45ML, OT63F, OT63FT, OT63ML, OT80F, OT80FT; 具体规格见附页

产品标准和技术要求

GB/T 14048.3-2017

上述产品符合《强制性产品认证实施规则 低压电器 低压元器件》
(CNCA-C03-02:2024) 的要求，特发此证。

发证日期：2024 年 07 月 15 日 有效期至：2029 年 07 月 14 日

证书信息和有效性可扫描下方二维码或登录发证机构网站查验，
也可在认监委网站 (www.cnca.gov.cn) 查询。



签发：

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司





中国国家强制性产品认证证书

证书编号: 2024010302658037

证书附页: 第 1 页 共 2 页

OT45ML, OT63F, OT63FT, OT63ML, OT80F, OT80FT

Uimp: 8kV;

Ui: 750V;

OT45ML:

Ith: 63A

Ue/Ie: 415/440/500V/63A(AC-21A,AC-22A)

415/440V/63A,500V/45A(AC-23A)

OT63F, OT63FT:

Ith: 63A

Ue/Ie: 415/440/500/690V/63A(AC-21A,AC-22A)

415/440V/63A,500V/45A,690V/20A(AC-23A)

OT63ML, OT80F, OT80FT:

Ith: 80A

Ue/Ie: 415/440/500/690V/80A(AC-21A,AC-22A)

415V/75A,440V/65A,500V/58A,690V/20A(AC-23A)

Icm(峰值): 2115A;

Icw: 1.5kA/1s;

Iq: OT45ML:500V/100kA;

OT63F, OT63FT, OT63ML, OT80F, OT80FT:500V/100kA;690V/50kA;

使用类别: AC-21A, AC-22A, AC-23A;

极数: 3P, 4P;

适用频率: 50/60Hz;

IP20(仅对前面板)

型号解释:

本页为证书附页, 应与证书主页同时使用。



中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司



中国国家强制性产品认证证书

证书编号: 2024010302658037

证书附页: 第 2 页 共 2 页

OT	80	F	4	N2	
					Mounting of the 4th pole 第四极的配置 N1=Fourth pole on the left side, 带第四极位于开关左侧 N2=Fourth pole on the right side, 带第四极位于开关右侧 N/PE=special type, N/PE 端子 blanco=basic 4th pole 基础款第四极
					Number of poles 极数 3--3pole 3 极 4--4pole 4 极 6--parallel connection by 2 of 3 pole switch disconnectors 6--2 组 3 极隔离开关并联 8--parallel connection by 2 of 4 pole switch disconnectors 8--2 组 4 极隔离开关并联
					Mounting 安装方式 F Base& DIN-rail mounting 底板和 DIN 导轨安装 FT Door mounting 门上安装 ML Base& DIN-rail mounting(white body) ML 底板和 DIN 导轨安装(白色壳体)
					Switch Size 电流等级(A) 45, 63, 80
					Switch disconnector 隔离开关型号

本页为证书附页, 应与证书主页同时使用。



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2024010302658037

NAME AND ADDRESS OF THE APPLICANT

ABB Oy
Muottitie 2A FI-65320 VAASA, Finland

NAME AND ADDRESS OF THE MANUFACTURER

ABB Oy
Muottitie 2A FI-65320 VAASA, Finland

NAME AND LOCATION OF THE FACTORY

ABB Oy
Muottitie 2A FI-65320 VAASA, Finland

PRODUCT NAME,MODEL AND SPECIFICATION

Switch-disconnector
OT45ML, OT63F, OT63FT, OT63ML, OT80F, OT80FT;see the appendix

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.3-2017

This is to certify that the above mentioned product(s) complies with the requirements of
implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

Valid from: Jul.15,2024

Valid until: Jul.14,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to
the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO. : 2024010302658037

Appendix: Page 1 of 1

OT45ML, OT63F, OT63FT, OT63ML, OT80F, OT80FT

Uimp: 8kV;

Ui: 750V;

OT45ML:

Ith: 63A

Ue/Ie: 415/440/500V/63A(AC-21A,AC-22A)

415/440V/63A,500V/45A(AC-23A)

OT63F, OT63FT:

Ith: 63A

Ue/Ie: 415/440/500/690V/63A(AC-21A,AC-22A)

415/440V/63A,500V/45A,690V/20A(AC-23A)

OT63ML, OT80F, OT80FT:

Ith: 80A

Ue/Ie: 415/440/500/690V/80A(AC-21A,AC-22A)

415V/75A,440V/65A,500V/58A,690V/20A(AC-23A)

Icm(Peak): 2115A;

Icw: 1.5kA/1s;

Iq: OT45ML:500V/100kA;

OT63F, OT63FT, OT63ML, OT80F, OT80FT:500V/100kA;690V/50kA;

Utilization Category: AC-21A, AC-22A, AC-23A;

Poles: 3P, 4P;

50/60Hz;

IP20(Only on the front panel)

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation