



MULTIPLE OF SENSOR



MULTIPLE OF SENSOR



Frames 800-5000A ANSI/UL 1066 CB
 Frames 800-6000A UL 489 CB

All Voltages: 600 Vac and below

Low-Voltage Circuit Breakers

EntelliGuard TU Trip Unit for EntelliGuard G and R (Retrofit) Circuit Breakers

UL489 and UL1066 Stored Energy Mechanism Circuit Breakers

Ground Fault

Applies to trip units manufactured with firmware version 08.00.26 and later

Curves apply at 50/60 Hertz and from -20°C to 55°C circuit breaker ambient temperature.

DES-124

Pickup Range
 Minimum 0.2X Sensor
 Maximum up to 1.0X Sensor
 Not to exceed 1200A