TYPICAL WIRING DIAGRAM

CONNECT LINE NEUTRAL TO PROPER TERMINAL ON RECEPTACLE



c UL us LISTED

POWER OUTLET 66FL

USE COPPER WIRE ONLY

RAINPROOF POWER OUTLET

MODEL.NO. U010F

20 AMPS

120 VOLTS A-C

TYPE 3R ENCLOSURE

WHEN CABINET HAS PROVISION FOR A CONDUIT HUB, SELECT FROM THE CHART BELOW.

CONDUIT SIZE	CLOSURE CAP	3/4	1	1 1/4	1 1/2
CAT.NO	B01	B07	B10	B12	B15

OVERCURRENT PROTECTION

SPACE FOR CLASS 'S' FUSE

20 AMPS MAXIMUM

USE ONLY 60 DEG.C (140 DEG.F) CONDUCTORS ON ALL FIELD INSTALLED LINE, LOAD AND NEUTRAL TERMINATIONS.

SHORT CIRCUIT CURRENT RATING OF THIS POWER OUTLET IS 10,000 RMS SYMMETRICAL AMPERES,240 VOLTS AC MAX. THE FUSE SHALL HAVE MINIMUM INTERRUPTING RATING OF 10,000 AMPS RMS. ADDITIONAL OR REPLACEMENT FUSES SHALL BE OF THE SAME MANUFACTURER AND TYPE DESIGNATION AND SHALL HAVE AN EQUAL OR GREATER SHORT CIRCUIT CURRENT RATING.

WIRE RANGE

CONNECTOR	COPPER SOLID	COPPER STRANDED
LINE-FH2 FUSEHOLDER	14-10	14-10
LOAD-VIA RECEPT./PLUG	14-10	14-10
NEUTRAL-DUPLEX	14-10	14-10
EQUIP.GRD.-GL2	12-8	12-2

SCREW TYPE	WIRE SIZE	TORQUE
SLOT	14-10	32-35
	8	36-40
	6-4	41-45
	3-2/0	45-50

SPACE FOR CLASS 'S' FUSE

DANGER

HAZARD OF ELECTRICAL SHOCK OR BURN. TURN OFF POWER BEFORE WORKING INSIDE THIS EQUIPMENT.

Ground-fault circuit-interrupter (GFCI) protection is not provided as part of this power outlet. If GFCI protection is required, the power outlet shall be installed on a GFCI protected circuit.

MIDWEST ELECTRIC PRODUCTS, INC
205 Gregson Drive
Cary, NC 27511
WWW.MIDWESTELECTRIC.COM

SAL245@

MNP600001

REV.C