

PRODUCT SPECIFICATION

STVVE3LS1X

Navigator Compact Self-Contained 32M IP20 Self-Test Wall Surface

Catalogue Number **STVVE3LS1X**
GID **7TCA091160R0570**
Warranty **3 Year/s Refer to ABB warranty terms & conditions**
Power Supply System **Self-Contained (individual battery)**
Mounting Method/Form **Wall Surface**
Housing Material **Metal**
Colour **White**
Dimensions (LxWxD) **358 x 185 x 71 mm**
Temperature Range **0 to 30°C**
Weight **1.86 Kg**

Emergency Duration (Hours) **3 Hours**
Battery **NiCd**
Monitoring Equipment **Automatic self test**
Lamp **1 x 2W LED**
Emergency Light Output (Lumens) **Not Applicable**
Average Lifespan light source (Hours) **100000 Hours**
Light Colour/Temperature/CRI **White / 4000 / 80**
Degree of Protection **IP20**

Type of Legend **Single Sided**
Exit Sign Viewing/Recognition Distance (m) **32**
Nominal Voltage **220-240v AC 50/60Hz**
Power Consumption **6.1 VA / 3.9 Watts**
Current **Nominal: 25.5mA (mA) Inrush: 0.7A**

Accessories

- XEN2V31** Down ISO7010 Legend
 - XEN3V31** Left ISO7010 Legend
 - XEN6V31** Right ISO7010 Legend
 - XEN5V31** Up ISO7010 Legend
 - XB01V31** Arabic English Legend
- VEBACK** Rear Trim Plate for Ceiling Mount



Exit Sign
STVVE3LS1X + XEN2V31

