

PRODUCT SPECIFICATION

## SR2-SWM3-G1

### Serenga 2 Self-Contained IP54 Self-Test Wall Surface

Catalogue Number **SR2-SWM3-G1**  
GID **7TCA091130R0471**

Warranty **4 Year/s Refer to ABB warranty terms & conditions**

Power Supply System **Self-Contained (individual battery)**

Mounting Method/Form **Ceiling Surface**

Housing Material **Aluminium/Plastic**

Colour **White**

Dimensions (LxWxD) **150 x 150 x 35 mm**

Temperature Range **5 to 40°C**

Weight **0.961 Kg**

Nominal Voltage **220-240v AC 50Hz**

Emergency Duration (Hours) **3 Hours**

Battery **NiMH**

Monitoring Equipment **Automatic self test**

Lamp **1 x 2W LED**

Light output in Emergency Operation **203 Lumens**

Average Lifespan light source (hours) **100000 Hours**

Light Colour/Temperature/CRI **White / 5600 / 70**

Degree of Protection **IP 54 IK tbc**

Wiring System **Maintained / non-maintained circuit**

Type of Legend **Not Applicable**

Exit Sign Viewing/Recognition Distance (m) **Not Applicable**

Power Consumption **3.5 VA / 3 Watts**

Nominal Current **15 (mA)**

Inrush Current **tbc A to 0.1 ms**

### Accessories

**SR2-LENS1** Lens A Escape route 2-4M Ceiling mount

**SR2-LENS2** Lens B Escape route 4-8M Ceiling mount OR Spot 2-4M Ceiling mount

**SR2-LENS3** Lens C Escape route 8-12M Ceiling mount

**SR2-LENS4** Lens D Open Area 2-4M Ceiling mount

**SR2-LENS5** Lens E Open Area 4-8M Ceiling mount

**SR2-LENS6** Lens E Open Area 8-12M Ceiling mount

**SR2-LENS7** Lens G Escape route 2-4M Wall mount

