

产品认证证书

II型自愿认证

证书编号: CQC2018010304128276

发证日期: 2022年03月30日

有效期至: 2032年03月29日

委托人名称 及注册地址	ABB France 11 Rue d' Arsonval 69680, Chassieu, FRANCE
制造商名称 及注册地址	ABB France 11 Rue d' Arsonval 69680, Chassieu, FRANCE
生产企业名称 及生产地址	ABB Bulgaria EOOD – Rakovski branch District Plovdiv, municipality Stryama, village Stryama 4142, Industrial Zone Rakovski, industrial road 1, nr. 14-18.
产品名称和系列、 规格、型号	切换电容器接触器 UA50,UA63,UA75: 详细参数及型号解释见附件
产品标准和技术要求	GB/T 14048.4-2020
认证模式	产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC12-000001-2020 认证规则的要求, 特发此证。

本证书为变更证书, 证书首次颁发日期: 2020年08月21日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



授权签字人

陈昕

签发

谢肇煦

中国质量认证中心



<http://www.cqc.com.cn>

中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666

C(2) 0147826

CERTIFICATE OF PRODUCT CERTIFICATION

TYPE II CQC CERTIFICATION

CERTIFICATE NO.: CQC2018010304128276

Valid from: Mar.30,2022

Valid until: Mar.29,2032

NAME AND REGISTERED ADDRESS OF THE APPLICANT	ABB France 11 Rue d' Arsonval 69680, Chassieu, FRANCE
NAME AND REGISTERED ADDRESS OF THE MANUFACTURER	ABB France 11 Rue d' Arsonval 69680, Chassieu, FRANCE
NAME AND LOCATION OF THE FACTORY	ABB Bulgaria EOOD – Rakovski branch District Plovdiv, municipality Stryama, village Stryama 4142, Industrial Zone Rakovski, industrial road 1, nr. 14-18.
PRODUCT NAME, MODEL AND SPECIFICATION	Contactors for capacitor switching UA50,UA63,UA75 : See the appendix
THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS	GB/T 14048.4-2020
TYPE OF CERTIFICATION SCHEMES	Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020.

Date of original issued: Aug.21,2020

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGN BY

陈昕

SIGNATURE

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE



<http://www.cqc.com.cn>

Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P. R. China

Tel: +86 10 83886666

C(2) 0147826

产品认证证书

II型自愿认证

证书编号: CQC2018010304128276

第1页 共2页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 147826

UA50,UA63,UA75

Uimp:8kV;

Ui: 1000V;

UA50:

Ith:100A;

AC-6b: Ue/Qe:220-230-240V/20kvar,400-415V/33kvar,440V/36kvar,
500-550V/40kvar,660-690V/55kvar;

Ie:51A;

UA63:

Ith:125A;

AC-6b: Ue/Qe:220-230-240V/25kvar,400-415V/45kvar,440V/50kvar,
500-550V/50kvar,660-690V/70kvar;

Ie:66A;

UA75:

Ith:125A;

AC-6b: Ue/Qe:220-230-240V/30kvar,400-415V/50kvar,440V/55kvar,
500-550V/62kvar,660-690V/75kvar;

Ie:76A;

Us: 24V 50/60Hz,42V 50/60Hz, 48V 50/60Hz,110V 50Hz/110-120V 60Hz,
220-230V 50Hz/230-240V 60Hz,380-400V 50Hz/400-415V 60Hz,
400-415V 50Hz/415-440V 60Hz;

IP10;

极数: 3P;

配用的辅助触头:(CAL5-11)(CQC2013010304604041)

Ith:16A;

AC-15:Ue/Ie: 24~127V/6A, 220~240V/4A, 380~440V/3A, 500~690V/2A;

DC-13:Ue/Ie: 24V/6A, 48V/2.8A, 72V/1A, 110~125V/0.55A, 220~250V/0.3A;

1NO1NC



中国质量认证中心



产品认证证书

II型自愿认证

证书编号: CQC2018010304128276

第2页 共2页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 147826

型号解释:

Example 例如: UA50-30-00-85				
UA	50	-30	-00	-85
I	II	III	IV	V

I - Name of series 系列名称
UA series UA 系列

II - Size of contactor 大小
50, 63, 75

III - Number of main contacts 主触头数量
30 = 3 NO- and 0 NC-contacts

IV - Number of auxiliary contacts 辅助触头数量
00 = No auxiliary pole provided.

11 = 1 NO- and 1 NC-contacts, side mounting CAL5-11

V - Coil code 线圈代号

Control voltage 控制电压		Coil code 线圈代号
50Hz	60Hz	
24	24	81
42	42	82
48	48	83
110	110-120	84
220-230	230-240	80
380-400	400-415	85
400-415	415-440	86



中国质量认证中心

