
TECHNICAL DATA SHEET

Terminals, ring

Nylon-insulated, double crimp

Spec-Kon[®]



Features:

- Easy Entry Double Crimp
- Corrosive resistant plating
- Color coded to wire size range

Maximum rating:

- 105°C Max
- 600 volts
- Copper conductors only

Application:

- ERG9004

Nylon-insulated ring terminals for wire termination of copper conductors ranging from 0.5mm² to 6mm²

Certifications / Standards:



Conforms to:

- IEC 60352-2

Materials / Finishes:

- Copper terminal
- Electro-Tin plated
- Nylon insulation

Terminals, ring:
Nylon-insulated, double crimp

Product selection

Drawing	Part no:	Wire size range (mm ²)	Color	Stud hole size		Dimensions (mm)			Crimping tool
				d2	L	F	W	D	
	R1.5-3NDC	0.5 - 1.5	Red	M3	18.2	4.8	5.5	4.4	ERG9004
	R1.5-35NDC	0.5 - 1.5	Red	M3.5	21.5	7.0	8.0	4.4	
	R1.5-4NDC	0.5 - 1.5	Red	M4	21.5	7.0	8.0	4.4	
	R1.5-5NDC	0.5 - 1.5	Red	M5	27.4	11.0	11.8	4.4	
	R1.5-6NDC	0.5 - 1.5	Red	M6	27.4	11.0	11.8	4.4	
	R1.5-8NDC	0.5 - 1.5	Red	M8	27.4	11.0	11.8	4.4	
	R1.5-10NDC	0.5 - 1.5	Red	M10	31.2	13.9	13.6	4.4	
	R2.5-3NDC	1.5 - 2.5	Blue	M3	18.5	4.7	6.6	5.0	
	R2.5-35NDC	1.5 - 2.5	Blue	M3.5	22.5	7.4	8.5	5.0	
	R2.5-4NDC	1.5 - 2.5	Blue	M4	22.5	7.8	8.5	5.0	
	R2.5-5NDC	1.5 - 2.5	Blue	M5	22.7	7.3	9.6	5.0	
	R2.5-6NDC	1.5 - 2.5	Blue	M6	27.6	11.0	12.0	5.0	
	R2.5-8NDC	1.5 - 2.5	Blue	M8	27.6	11.0	12.0	5.0	
	R2.5-10NDC	1.5 - 2.5	Blue	M10	31.2	13.6	13.6	5.0	
	R6-35NDC	4 - 6	Yellow	M3.5	22.7	6.1	7.2	7.0	
	R6-4NDC	4 - 6	Yellow	M4	26.0	8.3	9.5	7.0	
	R6-5NDC	4 - 6	Yellow	M5	26.0	8.3	9.5	7.0	
	R6-6NDC	4 - 6	Yellow	M6	29.5	10.5	12.0	7.0	
	R6-8NDC	4 - 6	Yellow	M8	34.0	13.5	15.0	7.0	
	R6-10NDC	4 - 6	Yellow	M10	34.0	13.5	15.0	7.0	
R6-12NDC	5 - 6	Yellow	M12	38.6	16.0	19.2	7.0		

Note: Products must be installed in accordance with applicable national and local electrical codes.