

AC500 CPU Firmware / Programming Software Overview

ABB Automation Products GmbH

Eppelheimer Str. 82

D-69123 Heidelberg Germany

Telephone: +49 62 21 701 1444

Fax: +49 62 21 701 1382

Email: plc.sales@de.abb.com

Internet: www.abb.com/plc

Doc.-Nr: **3ADR020152M0401**

Date	Description	Author	Index
08.11.16	Creation of the document	ReAm	-
12.06.17	New FW V2.6 added, AC500 V3 CPU added	ReAm	A
11.04.18	Introduction from V2.7.2 and V2.3.6 for flash replacement	ReAm	B
14.05.18	Introduction of AC500-eCo CPU overview	ReAm	C
28.05.18	Modification address	ReAm	D

Note: This document summarizes the FW / SW versions and production index from the available AC500 CPUs. It gives also the dependencies between FW/SW versions and is give as information. For each FW or SW version, a link to the release notes is provided if existing.

Any liability of ABB – regardless of the legal grounds – shall be excluded. In particular any warranty or defect liability for the Products (whether hardware, software or firmware) or for any documentation or information related thereto and any damage or losses resulting there from shall be excluded, e.g. in view of correctness, completeness, applicability of the Products/documentation/information or the same not being up-to-date and free of any defect.

Active AC500 V2 Process Modules

Type	Part Number Production Index	CPU FW V2.0.2	CPU FW V2.0.4	CPU FW V2.0.6	CPU FW V2.1.3	CPU FW V2.2.0	CPU FW V2.2.1	CPU FW V2.3.0	CPU FW V2.3.3	CPU FW V2.3.6	CPU FW V2.4.2	CPU FW V2.4.4	CPU FW V2.4.6	CPU FW V2.5.1	CPU FW V2.5.2	CPU FW V2.5.3	CPU FW V2.6.0	CPU FW V2.7.0	CPU FW V2.7.2
Launch date						Jul. 12		Mrz. 13	Jan. 14	Mrz. 18	Mrz. 15	Sep. 15	Nov. 15	Mrz. 16	Apr. 16	Sep. 16	Mai. 17	Apr. 18	Apr. 18
PM572	1SAP130200R0200	CBP V2.0.0 A2	-	CBP V2.0.1 A4	CBP V2.1.0 A5	CBP V2.2.0 A6	-	AB 1.0.0 / CBP V2.3.0 A7	AB 1.0.1 A8	-	AB 1.1.1 B0	AB 1.1.2 B1	-	-	AB 1.2.2 B2	AB 1.2.3 B3	AB 2.0.1 B4	-	AB 2.1.1 C0
PM573-ETH	1SAP130300R0271	CBP V2.0.0 A2	-	CBP V2.0.1 A4	CBP V2.1.0 A5	CBP V2.2.0 A6	-	AB 1.0.0 / CBP V2.3.0 A7	AB 1.0.1 A8	-	AB 1.1.1 B0	AB 1.1.2 B1	-	-	AB 1.2.2 B2	AB 1.2.3 B3 / B4	AB 2.0.1 B5	-	AB 2.1.1 C0
PM582	1SAP140200R0201	CBP V2.0.0 A2	-	CBP V2.0.1 A4	CBP V2.1.0 A5	CBP V2.2.0 A6	-	AB 1.0.0 / CBP V2.3.0 A7	AB 1.0.1 A8	-	AB 1.1.1 B0	AB 1.1.2 B1	-	-	AB 1.2.2 B2	AB 1.2.3 B3	AB 2.0.1 B4	-	AB 2.1.1 C0
PM583-ETH	1SAP140300R0271	CBP V2.0.0 A2	-	CBP V2.0.1 A4	CBP V2.1.0 A5	CBP V2.2.0 A6	-	AB 1.0.0 / CBP V2.3.0 A7	AB 1.0.1 A8	-	AB 1.1.1 B0	AB 1.1.2 B1	-	-	AB 1.2.2 B2	AB 1.2.3 B3	AB 2.0.1 B4	-	AB 2.1.1 C0
PM585-ETH	1SAP140500R0271													AB 1.2.1 A2	AB 1.2.2 A4	AB 1.2.3 A5	AB 2.0.1 A6	-	AB 2.1.1 A7
PM590-ARC	1SAP150000R0261										AB 1.1.1 A2	AB 1.1.2 A3	-	AB 1.2.1 A4	AB 1.2.2 A5	AB 1.2.3 A6	AB 2.0.1 A7	-	AB 2.1.1 A8
PM590-ETH	1SAP150000R0271			CBP V2.0.1 D4	CBP V2.1.0 D5-D6	CBP V2.2.0 D7	-	AB 1.0.0 / CBP V2.3.0 D8	AB 1.0.1 D9	-	AB 1.1.1 E1	AB 1.1.2 E2	-	AB 1.2.1 E3	AB 1.2.2 E4	AB 1.2.3 E5	AB 2.0.1 E6	-	AB 2.1.1 E7
PM591-ETH	1SAP150100R0271			CBP V2.0.1 D4	CBP V2.1.0 D5-D6	CBP V2.2.0 D7	-	AB 1.0.0 / CBP V2.3.0 D8	AB 1.0.1 D9	-	AB 1.1.1 E1	AB 1.1.2 E2	-	AB 1.2.1 E3	AB 1.2.2 E4	AB 1.2.3 E5	AB 2.0.1 E6	-	AB 2.1.1 E7
PM591-2ETH	1SAP150100R0277										AB 1.1.1 A5	AB 1.1.2 A6	-	AB 1.2.1 A7	AB 1.2.2 A8	AB 1.2.3 A9	AB 2.0.1 A0	-	AB 2.1.1 B0
PM592-ETH	1SAP150200R0271				CBP V2.1.0 A6	CBP V2.2.0 A7	-	AB 1.0.0 / CBP V2.3.0 A8	AB 1.0.1 A9	-	AB 1.1.1 B1	AB 1.1.2 B2	-	AB 1.2.1 B3	AB 1.2.2 B4	AB 1.2.3 B5	AB 2.0.1 B6	-	AB 2.1.1 B7
PM595-4ETH-F	1SAP155500R0279										AB 1.1.1 A7	AB 1.1.2 A8	-	AB 1.2.1 A9	AB 1.2.2 B0	AB 1.2.3 B1	AB 2.0.1 B2	AB 2.1.1 B3	
CM574-RS	1SAP170400R0201		CBP V2.0.0	-	CBP V2.1.0	CBP V2.2.0	-	-	-	-	-	AB 1.1.2 A6	AB 1.1.2 A7	-	-	-	-	-	AB 2.1.1 C0
CM574-RCOM	1SAP170401R0201		CBP V2.0.0	-	CBP V2.1.0	CBP V2.2.0	-	-	-	-	-	AB 1.1.2 A6	AB 1.1.2 A7	-	-	-	-	-	AB 2.1.1 C0
PM573-ETH-XC	1SAP330300R0271	CBP V2.0.0 A1	-	CBP V2.0.1 A2	CBP V2.1.0 A3	CBP V2.2.0 B0	-	AB 1.0.0 / CBP V2.3.0 B1	AB 1.0.1 B2	-	AB 1.1.1 B4	AB 1.1.2 B5	-	-	AB 1.2.2 B6	AB 1.2.3 B7 / B8	AB 2.0.1 B9	-	AB 2.1.1 C0
PM582-XC	1SAP340200R0201	CBP V2.0.0 A1	-	CBP V2.0.1 A2	CBP V2.1.0 A3	CBP V2.2.0 B0	-	AB 1.0.0 / CBP V2.3.0 B1	AB 1.0.1 B2	-	AB 1.1.1 B4	AB 1.1.2 B5	-	-	AB 1.2.2 B6	AB 1.2.3 B7	AB 2.0.1 B8	-	AB 2.1.1 C0
PM583-ETH-XC	1SAP340300R0271	CBP V2.0.0 A1	-	CBP V2.0.1 A2	CBP V2.1.0 A3	CBP V2.2.0 B0	-	AB 1.0.0 / CBP V2.3.0 B1	AB 1.0.1 B2	-	AB 1.1.1 B4	AB 1.1.2 B5	-	-	AB 1.2.2 B6	AB 1.2.3 B7	AB 2.0.1 B8	-	AB 2.1.1 C0
PM591-ETH-XC	1SAP350100R0271			CBP V2.0.1 A3	CBP V2.1.0 A4-A5	CBP V2.2.0 B0	-	AB 1.0.0 / CBP V2.3.0 B1	AB 1.0.1 B2	-	AB 1.1.1 B4	AB 1.1.2 B5	-	AB 1.2.1 B6	AB 1.2.2 B7	AB 1.2.3 B8	AB 2.0.1 B9	-	AB 2.1.1 C0
PM592-ETH-XC	1SAP350200R0271				CBP V2.1.0 A4-A5	CBP V2.2.0 B0	-	AB 1.0.0 / CBP V2.3.0 B1	AB 1.0.1 B2	-	AB 1.1.1 B4	AB 1.1.2 B5	-	AB 1.2.1 B6	AB 1.2.2 B7	AB 1.2.3 B8	AB 2.0.1 B9	-	AB 2.1.1 C0
PM595-4ETH-M-XC	1SAP351500R0279										AB 1.1.1 A6	AB 1.1.2 A7	-	AB 1.2.1 A8	AB 1.2.2 A9	AB 1.2.3 B0	AB 2.0.1 B1	AB 2.1.1 B2	

Product launch
 No new FW version available, previous still active
 From that Index, the CPU couldn't be downgraded anymore

-

Active AC500-eCo V2 CPUs

Type	Part Number Production Index	CPU FW V2.0.2	CPU FW V2.0.4	CPU FW V2.0.6	CPU FW V2.1.3	CPU FW V2.2.0	CPU FW V2.2.1	CPU FW V2.3.0	CPU FW V2.3.1	CPU FW V2.3.3	CPU FW V2.4.2	CPU FW V2.4.4	CPU FW V2.4.6	CPU FW V2.5.1	CPU FW V2.5.2	CPU FW V2.5.3	CPU FW V2.6.0	CPU FW V2.7.0	CPU FW V2.7.2
	Launch date					Mai. 12		Mrz. 13	Jun. 13	Jan. 14	Mrz. 15	Sep. 15	Nov. 15	Mrz. 16	Apr. 16	Aug. 16	Mai. 17	Apr. 18	Apr. 18
PM554-TP	1SAP120600R0001					CBP V2.2.0 A2	-	CBP V2.2.0 A3	CBP V2.2.0 A4	CBP V2.3.0 A5,A6	AB1.0.0/ AB1.1.0 A7 -> A9	-	-	AB1.0.0/ AB1.2.1 A10,B1->B3	-	-	-	-	AB2.1.1 CO
PM554-RP	1SAP120700R0001					CBP V2.2.0 A2	-	CBP V2.2.0 A3	CBP V2.2.0 A4	CBP V2.3.0 A5,A6	AB1.0.0/ AB1.1.0 A7, A8	-	-	AB1.0.0/ AB1.2.1 A9,B1,B2	-	-	-	-	AB2.1.1 CO
PM554-RP-AC	1SAP120800R0001					CBP V2.2.0 A2	-	CBP V2.2.0 A3	CBP V2.2.0 A4	CBP V2.3.0 A5,A6	AB1.0.0/ AB1.1.0 A7, A8	-	-	AB1.0.0/ AB1.2.1 A9,B1,B2	-	-	-	-	AB2.1.1 CO
PM554-TP-ETH	1SAP120600R0071					CBP V2.2.0 A2	-	CBP V2.2.0 A3	CBP V2.2.0 A4	CBP V2.3.0 A5	AB1.0.0/ AB1.1.0 A6 -> A8	-	-	AB1.0.0/ AB1.2.1 A9,B1,B2	-	-	-	-	AB2.1.1 CO
PM556-TP-ETH	1SAP121200R0071								CBP V2.2.0 A0	CBP V2.3.0 A1	AB1.0.0/ AB1.1.0 A2 -> A4	-	-	AB1.0.0/ AB1.2.1 A5 -> A7	-	-	-	-	AB2.1.1 CO
PM564-TP	1SAP120900R0001					CBP V2.2.0 A2	-	CBP V2.2.0 A3	CBP V2.2.0 A4	CBP V2.3.0 A5,A6	AB1.0.0/ AB1.1.0 A7 -> A9	-	-	AB1.0.0/ AB1.2.1 A10,B1->B3	-	-	-	-	AB2.1.1 CO
PM564-RP	1SAP121000R0001					CBP V2.2.0 A2	-	CBP V2.2.0 A3	CBP V2.2.0 A4	CBP V2.3.0 A5,A6	AB1.0.0/ AB1.1.0 A7,A8	-	-	AB1.0.0/ AB1.2.1 A9,B1,B2	-	-	-	-	AB2.1.1 CO
PM564-RP-AC	1SAP121100R0001					CBP V2.2.0 A2	-	CBP V2.2.0 A3	CBP V2.2.0 A4	CBP V2.3.0 A5,A6	AB1.0.0/ AB1.1.0 A7,A8	-	-	AB1.0.0/ AB1.2.1 A9,B1,B2	-	-	-	-	AB2.1.1 CO
PM564-TP-ETH	1SAP120900R0071					CBP V2.2.0 A2	-	CBP V2.2.0 A3	CBP V2.2.0 A4	CBP V2.3.0 A5	AB1.0.0/ AB1.1.0 A6 -> A8	-	-	AB1.0.0/ AB1.2.1 A9,B1,B2	-	-	-	-	AB2.1.1 CO
PM564-RP-ETH	1SAP121000R0071					CBP V2.2.0 A2	-	CBP V2.2.0 A3	CBP V2.2.0 A4	CBP V2.3.0 A5	AB1.0.0/ AB1.1.0 A6,A7	-	-	AB1.0.0/ AB1.2.1 A8,A9,B1	-	-	-	-	AB2.1.1 CO
PM564-RP-ETH-AC	1SAP121100R0071					CBP V2.2.0 A2	-	CBP V2.2.0 A3	CBP V2.2.0 A4	CBP V2.3.0 A5	AB1.0.0/ AB1.1.0 A6,A7	-	-	AB1.0.0/ AB1.2.1 A8,A9,B1	-	-	-	-	AB2.1.1 CO
PM566-TP-ETH	1SAP121500R0071										AB1.0.0/ AB1.1.0 A1,A2	-	-	AB1.0.0/ AB1.2.1 A3 -> A5	-	-	-	-	AB2.1.1 CO
PM556-TP-ETH(Emerson)	1SAP121200R1371						CBP V2.2.0 A1,A2	CBP V2.2.0 A3	CBP V2.2.0 A4	-	-	-	-	-	-	-	-	-	-
PM556-TP-ETH(Emerson)	1SAP121200R2371						CBP V2.2.0 A1,A2	CBP V2.2.0 A3	CBP V2.2.0 A4	CBP V2.3.0 A5	AB1.0.0/ AB1.1.0 A6 -> A8	-	-	AB1.0.0/ AB1.2.1 A9,B1,B2	-	-	-	-	AB2.1.1 CO

Product launch
No new FW version available, previous still active

-

Legacy AC500 V2 Process Modules

Type	Part Number Production Index	Lifecycle status	Released Firmware version / Programming Software version											
			CPU FW V1.4.2	CPU FW V1.4.4	CPU FW V1.4.5	CPU FW V2.0.2	CPU FW V2.0.4	CPU FW V2.0.6	CPU FW V2.1.3	CPU FW V2.2.0	CPU FW V2.2.1	CPU FW V2.3.0	CPU FW V2.3.3	CPU FW V2.4.2
PM571	1SAP130100R0200	Limited	CBP V1.3.0 A1	-	-	-	-	-	-	-	-	-	-	-
PM571-ARCNET	1SAP130100R0260	Limited	CBP V1.3.0 A1	-	-	-	-	-	-	-	-	-	-	-
PM571-ETH	1SAP130100R0270	Limited	CBP V1.3.0 A1	-	-	-	-	-	-	-	-	-	-	-
PM581	1SAP140100R0200	Limited	CBP V1.3.0 A1	-	-	-	-	-	-	-	-	-	-	-
PM581-ARCNET	1SAP140100R0260	Limited	CBP V1.3.0 A1	-	-	-	-	-	-	-	-	-	-	-
PM581-ETH	1SAP140100R0270	Limited	CBP V1.3.0 A1	-	-	-	-	-	-	-	-	-	-	-
PM582	1SAP140200R0200	Limited	CBP V1.3.0 A1	-	-	-	-	-	-	-	-	-	-	-
PM582-ARCNET	1SAP140200R0260	Limited	CBP V1.3.0 A1	-	-	-	-	-	-	-	-	-	-	-
PM582-ETH	1SAP140200R0270	Limited	CBP V1.3.0 A1	-	-	-	-	-	-	-	-	-	-	-
PM590	1SAP150000R0200	Limited			CBP V1.3.2 D3	-	-	-	-	-	-	-	-	-
PM590-ARCNET	1SAP150000R0260	Limited			CBP V1.3.2 D3	-	-	-	-	-	-	-	-	-
PM590-ETH	1SAP150000R0270	Limited			CBP V1.3.2 D3	-	-	-	-	-	-	-	-	-
PM591	1SAP150100R0200	Limited			CBP V1.3.2 D3	-	-	-	-	-	-	-	-	-
PM591-ARCNET	1SAP150100R0260	Limited			CBP V1.3.2 D3	-	-	-	-	-	-	-	-	-
PM591-ETH	1SAP150100R0270	Limited			CBP V1.3.2 D3	-	-	-	-	-	-	-	-	-
CM574-RS	1SAP170400R0101	Limited		CBP V1.3.1 A3	-	-	-	-	-	-	-	-	-	-
CM574-RCOM	1SAP170401R0101	Limited		CBP V1.3.1 A3	-	-	-	-	-	-	-	-	-	-

Product launch
No new FW version available, previous still active

-

Legacy AC500-eCo V1 CPUs

Type	Part Number Production Index	Lifecycle Status	CPU FW V1.3.4	CPU FW V1.4.4	CPU FW V1.4.5	CPU FW V2.0.2	CPU FW V2.0.4	CPU FW V2.0.6	CPU FW V2.1.3	CPU FW V2.2.0	CPU FW V2.2.1	CPU FW V2.3.0	CPU FW V2.3.3	CPU FW V2.4.2	CPU FW V2.4.4	CPU FW V2.4.6	CPU FW V2.5.1	CPU FW V2.5.2	CPU FW V2.5.3	CPU FW V2.6.0	CPU FW V2.7.0	CPU FW V2.7.2
Launch date						Sep. 10		Jun. 11	Sep. 11			Mrz. 13	Jan. 14	Mrz. 15	Sep. 15	Nov. 15	Mrz. 16	Apr. 16	Aug. 16	Mai. 17	Apr. 18	Apr. 18
PM554-T	1TNE968900R0100	Limited	CBP V1.3.0 A1,A2	-	-	-	-	CBP V2.0.2 A2,A3	CBP V2.1.0 A4,A5	-	-	CBP V2.2.0 A6	-	-	-	-	-	-	-	-	-	-
PM554-R	1TNE968900R0200	Limited	CBP V1.3.0 A1,A2	-	-	-	-	CBP V2.0.2 A2,A3	CBP V2.1.0 A4,A5	-	-	CBP V2.2.0 A6	-	-	-	-	-	-	-	-	-	-
PM554-R-AC	1TNE968900R0220	Limited	CBP V1.3.0 A1,A2	-	-	-	-	CBP V2.0.2 A2,A3	CBP V2.1.0 A4,A5	-	-	CBP V2.2.0 A6	-	-	-	-	-	-	-	-	-	-
PM554-T-ETH	1TNE968900R0110	Limited				CBP V2.0.0 A0 -> A2	-	CBP V2.0.2 A2,A3	CBP V2.1.0 A4,A5	-	-	CBP V2.2.0 A6	-	-	-	-	-	-	-	-	-	-
PM564-T	1TNE968900R1100	Limited	CBP V1.3.0 A1,A2	-	-	-	-	CBP V2.0.2 A2,A3	CBP V2.1.0 A4,A5	-	-	CBP V2.2.0 A6	-	-	-	-	-	-	-	-	-	-
PM564-R	1TNE968900R1200	Limited	CBP V1.3.0 A1,A2	-	-	-	-	CBP V2.0.2 A2,A3	CBP V2.1.0 A4,A5	-	-	CBP V2.2.0 A6	-	-	-	-	-	-	-	-	-	-
PM564-R-AC	1TNE968900R1220	Limited	CBP V1.3.0 A1,A2	-	-	-	-	CBP V2.0.2 A2,A3	CBP V2.1.0 A4,A5	-	-	CBP V2.2.0 A6	-	-	-	-	-	-	-	-	-	-
PM564-T-ETH	1TNE968900R1110	Limited				CBP V2.0.0 A0 -> A2	-	CBP V2.0.2 A2,A3	CBP V2.1.0 A4,A5	-	-	CBP V2.2.0 A6	-	-	-	-	-	-	-	-	-	-
PM564-R-ETH	1TNE968900R1210	Limited				CBP V2.0.0 A0 -> A2	-	CBP V2.0.2 A2,A3	CBP V2.1.0 A4,A5	-	-	CBP V2.2.0 A6	-	-	-	-	-	-	-	-	-	-
PM564-R-ETH-AC	1TNE968900R1211	Limited				CBP V2.0.0 A0 -> A2	-	CBP V2.0.2 A2,A3	CBP V2.1.0 A4,A5	-	-	CBP V2.2.0 A6	-	-	-	-	-	-	-	-	-	-

Product launch
No new FW version available, previous still active

-

AC500 V2 CPUs
HW/FW Compatibility - Downgradability

Type	P/N	HW Production Index	Old Flash	New Flash	FW 2.0.2	FW 2.0.4	FW 2.0.6	FW 2.1.3	FW 2.2.x	FW 2.3.x	FW 2.3.6	FW2.4.x	FW 2.5.1	FW 2.5.2	FW 2.5.3	FW2.6.x	FW 2.7.0	FW 2.7.2	... > FW 2.7.2	e.g. FW 2.8.x	
Micro PLC	PM572	1SAP130200R0200	Index -> B4	X	Downgrade possible, e.g. FW 2.7.x delivered downgraded up to FW 2.0.2																
	PM572	1SAP130200R0200	e.g. Index C0 ->	X	Downgrade not possible							Possible	Downgrade not possible to FW smaller than V2.7.2, only to V2.3.6					downgrade only to smallest FW V2.7.2 or only to the V2.3.6			
	PM573-ETH	1SAP130300R0271	Index -> B2	X	Downgrade possible																
	PM573-ETH-XC	1SAP330300R0271	Index -> B7	X	e.g. delivered FW 2.5.x downgraded up to FW 2.0.2																
	PM573-ETH	1SAP130300R0271	Index B3->	X	Downgrade not possible to FW smaller than V2.5.3										Downgrade possible only to smallest FW V2.5.3						
	PM573-ETH-XC	1SAP330300R0271	Index B8->	X	e.g. delivered FW 2.7.x downgraded to FW 2.5.3																
	PM573-ETH	1SAP130300R0271	e.g. Index C0 ->	X	Downgrade not possible							Possible	Downgrade not possible to FW smaller than V2.7.2, only to V2.3.6					downgrade only to smallest FW V2.7.2 or only to the V2.3.6			
PM573-ETH-XC	1SAP330300R0271	e.g. Index C0 ->	X	Downgrade not possible							Possible	Downgrade not possible to FW smaller than V2.7.2, only to V2.3.6					downgrade only to smallest FW V2.7.2 or only to the V2.3.6				
CM	CM574-RS	1SAP170400R0201	Index -> B0	X	Not existing		Downgrade possible														
	CM574-RS	1SAP170400R0201	e.g. Index B1 ->	X	Not existing		e.g. delivered FW 2.7.x downgraded up to FW 2.1.3														
	CM574-RCOM	1SAP170401R0201	Index -> B0	X	Not existing		Downgrade possible														
	CM574-RCOM	1SAP170401R0201	e.g. Index B1 ->	X	Not existing		e.g. delivered FW 2.7.x downgraded up to FW 2.1.3														
Mini PLC	PM582	1SAP140200R0201	Index -> B4	X	Downgrade possible																
	PM582-XC	1SAP340200R0201	Index -> B8	X	e.g. delivered FW 2.5.x downgraded up to FW 2.0.2																
	PM582	1SAP140200R0201	e.g. Index C0 ->	X	Downgrade not possible							Possible	Downgrade not possible to FW smaller than V2.7.2, only to V2.3.6					downgrade only to smallest FW V2.7.2 or only to the V2.3.6			
	PM582-XC	1SAP340200R0201	e.g. Index C0 ->	X	Downgrade not possible							Possible	Downgrade not possible to FW smaller than V2.7.2, only to V2.3.6					downgrade only to smallest FW V2.7.2 or only to the V2.3.6			
	PM583-ETH	1SAP140300R0271	Index -> B4	X	Downgrade possible																
	PM583-ETH-XC	1SAP340300R0271	Index -> B8	X	e.g. delivered FW 2.5.x downgraded up to FW 2.0.2																
	PM583-ETH	1SAP140300R0271	e.g. Index C0 ->	X	Downgrade not possible							Possible	Downgrade not possible to FW smaller than V2.7.2, only to V2.3.6					downgrade only to smallest FW V2.7.2 or only to the V2.3.6			
PM583-ETH-XC	1SAP340300R0271	e.g. Index C0 ->	X	Downgrade not possible							Possible	Downgrade not possible to FW smaller than V2.7.2, only to V2.3.6					downgrade only to smallest FW V2.7.2 or only to the V2.3.6				
PM585-ETH	1SAP140500R0271	Index -> A7	X	Not existing								Downgrade possible									
PM585-ETH	1SAP140500R0271	Index A8 ->	X	Not existing								e.g. delivered FW 2.7.x downgraded to FW 2.5.1									
Midi PLC	PM590-ARC	1SAP150000R0261	Index ->A7	X	Not existing							Downgrade possible									
	PM590-ARC	1SAP150000R0261	Index A8 ->	X	Not existing							e.g. delivered FW 2.7.x downgraded up to FW 2.4.2									
	PM590-ETH	1SAP150000R0271	Index -> E6	X	Not existing		Downgrade possible														
	PM590-ETH	1SAP150000R0271	Index E7 ->	X	Not existing		e.g. delivered FW 2.7.x downgraded up to FW 2.0.6														
	PM591-ETH	1SAP150100R0271	Index -> E6	X	Not existing		Downgrade possible														
	PM591-ETH	1SAP150100R0271	Index E7 ->	X	Not existing		e.g. delivered FW 2.7.x downgraded up to FW 2.0.6														
	PM591-ETH-XC	1SAP350100R0271	Index -> B9	X	Not existing		Downgrade possible														
	PM591-ETH-XC	1SAP350100R0271	Index C0 ->	X	Not existing		e.g. delivered FW 2.7.x downgraded up to FW 2.0.6														
	PM591-2ETH	1SAP150100R0277	Index -> A9	X	Not existing								Downgrade possible								
	PM591-2ETH	1SAP150100R0277	Index B0 ->	X	Not existing								e.g. delivered FW 2.7.x downgraded to FW 2.4.2								
	PM592-ETH	1SAP150200R0271	Index -> B6	X	Not existing		Downgrade possible														
	PM592-ETH	1SAP150200R0271	Index B7 ->	X	Not existing		e.g. delivered FW 2.7.x downgraded up to FW 2.1.3														
	PM592-ETH-XC	1SAP350200R0271	Index -> B9	X	Not existing		Downgrade possible														
PM592-ETH-XC	1SAP350200R0271	Index C0 ->	X	Not existing		e.g. delivered FW 2.7.x downgraded up to FW 2.1.3															
Large PLC	PM595-4ETH-F	1SAP155500R0279	Index -> B2	X	Not existing							Downgrade possible									
	PM595-4ETH-F	1SAP155500R0279	Index B3 ->	X	Not existing							e.g. delivered FW 2.7.x downgraded up to FW 2.4.2									
	PM595-4ETH-M-XC	1SAP351500R0279	Index -> B1	X	Not existing							Downgrade possible									
	PM595-4ETH-M-XC	1SAP351500R0279	Index B2 ->	X	Not existing							e.g. delivered FW 2.7.x downgraded up to FW 2.4.2									

New FW created for the CPU with new Flash

**AC500-eCo CPUs
HW/FW Compatibility - Downgradability**

	Type	P/N	Index	Old flash	New flash	Downgradability											... > FW 2.7.2	e.g. FW 2.8.x	
						FW V1.3.4	FW V2.0.2	FW V2.0.6	FW V2.1.3	FW V2.2.0	FW V2.2.1	FW V2.3.0	FW V2.3.1	FW V2.3.3	FW V2.4.2	FW V2.5.1			FW V2.7.2
eCo - Non ETH	PM554-TP	1SAP120600R0001	A2 -> A4; A6 -> A9; B0 -> B3	✓		Not existing	Downgrade is possible; down to V2.0.2												
			C0 -> ...		✓		Downgrade impossible											downgrade only to smallest FW V2.7.2	
	PM564-TP	1SAP120900R0001	A2 -> A4; A6 -> A9; B0 -> B3	✓		Not existing	Downgrade is possible; down to V2.0.2												
			C0 -> ...		✓		Downgrade impossible											downgrade only to smallest FW V2.7.2	
	PM554-RP	1SAP120700R0001	A2 -> A4; A6 -> A9; B0 -> B2	✓		Not existing	Downgrade is possible; down to V2.0.2												
			C0 -> ...		✓		Downgrade impossible											downgrade only to smallest FW V2.7.2	
PM564-RP	1SAP121000R0001	A2 -> A4; A6 -> A9; B0 -> B2	✓		Not existing	Downgrade is possible; down to V2.0.2													
		C0 -> ...		✓		Downgrade impossible											downgrade only to smallest FW V2.7.2		
PM554-RP-AC	1SAP120800R0001	A2 -> A4; A6 -> A9; B0 -> B2	✓		Not existing	Downgrade is possible; down to V2.0.2													
		C0 -> ...		✓		Downgrade impossible											downgrade only to smallest FW V2.7.2		
PM564-RP-AC	1SAP121100R0001	A2 -> A4; A6 -> A9; B0 -> B2	✓		Not existing	Downgrade is possible; down to V2.0.2													
		C0 -> ...		✓		Downgrade impossible											downgrade only to smallest FW V2.7.2		
eCo - ETH	PM554-TP-ETH	1SAP120600R0071	A2 -> A9; B0 -> B2	✓		Not existing	Downgrade is possible; down to V2.0.2												
			C0 -> ...		✓		Downgrade impossible											downgrade only to smallest FW V2.7.2	
	PM564-TP-ETH	1SAP120900R0071	A2 -> A9; B0 -> B2	✓		Not existing	Downgrade is possible; down to V2.0.2												
			C0 -> ...		✓		Downgrade impossible											downgrade only to smallest FW V2.7.2	
	PM564-RP-ETH	1SAP121000R0071	A2 -> A9; B0 -> B1	✓		Not existing	Downgrade is possible; down to V2.0.2												
			C0 -> ...		✓		Downgrade impossible											downgrade only to smallest FW V2.7.2	
PM564-RP-ETH-AC	1SAP121100R0071	A2 -> A9; B0 -> B1	✓		Not existing	Downgrade is possible; down to V2.0.2													
		C0 -> ...		✓		Downgrade impossible											downgrade only to smallest FW V2.7.2		
PM556-TP-ETH	1SAP121200R0071	A1 -> A7	✓		Not existing	Downgrade is possible; down to V2.0.2													
		C0 -> ...		✓		Downgrade impossible											downgrade only to smallest FW V2.7.2		
PM566-TP-ETH	1SAP121500R0071	A1 -> A5	✓		Not existing	Downgrade is possible; down to V2.0.2													
		C0 -> ...		✓		Downgrade impossible											downgrade only to smallest FW V2.7.2		

New FW created for the CPU with new Flash