



## EVA-R-DWI

Self-contained 2 watt, round white maintained recess led luminaire, including automatic self test, series Evago. Light distribution: wide (W), for example canteens, RAL9003

### Product Information

Type	EVA-R-DWI
Catalog number	5520217064
Category_	Escape route lighting
GTIN	08713812762128
GID	7TCA091160R0338
Serie	Evago
Warranty (Year)	5



### Characteristics

Power supply system	Self-contained individual battery
Continuous operation	Yes
Mounting Method	Ceiling
Mounting form	Recess
Material housing	Aluminium / plastic
Colour housing	White
Material	Aluminium / polycarbonate
Colour	White
Length (mm)	316
Width (mm)	100
Height/depth (mm)	78
Maximum outer diameter (mm)	100
Built-in length (mm)	316
Built-in width (mm)	68
Built-in diameter (mm)	68
Built-in depth (mm)	35
Nominal voltage (V)	230
Voltage type	AC
Duration (hours)	1
Battery	NiMH
Monitoring equipment	Automatic self test
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	2
Number of lamps	1
Light output in emergency operation (lm)	245
Average lifespan light source (hours)	100.000
Colour of light	White
Colour temperature (K)	5600
CRI	70
Protection class	II
Degree of protection (IP)	42
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Not applicable
Circuit	Other
Power consumption maintained mode (W)	3 / 2
Apparent power consumption maintained mode (VA)	3,5 / 2,85

Nominal current (mA)	15
Powerfactor	0,85 / 0,7
Temperature range (°C)	5 ~ +35

#### **Article Details**

Product class	Emergency luminaire
E-code	EC001957
Discount group	30901
Harmonized code	9405408440
GLN	8713812000008

#### **Ordering information**

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

#### **Supply Information**

Weight (kg)	0,579
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	225 x 170 x 62