

Stanilite®

Platinum exit LED edgelit Quickfit® Nexus®

p-Range



Range

Platinum range

Product group

Exit LED edgelit



Features

- 5 year warranty
- High emergency classification
- LED technology 100,000 hours plus lamp life
- Low power consumption and LED light source for reduced operation and maintenance costs
- Advance charging technology combined with Lithium iron phosphate battery for long life and low maintenance
- Nexus monitored, either cabled or wireless
- Architecturally pleasing slim line design
- Quickfit unique steel slide connect bracket for quick installation and easy maintenance
- Includes all pictograph diffuser options
- Universal wall/ceiling mounting, can also be rod or wire suspended
- Retrofit capability; fits into any existing Quickfit mounting bracket

| Catalogue no. | Description |
|-----------------------|--|
| Nexus products | |
| PLQNXSLEDP | Platinum exit LED edgelit Quickfit Nexus LX pictograph |
| PLQNRFLEDP | Platinum exit LED edgelit Quickfit Nexus RF pictograph |
| Spare parts | |
| 03-01305P | Battery LiFePO4 3.2V 1.5Ah |



| Dimensions | | | |
|-------------------|--------------------------------|-------|------------------------|
| | Length | Width | Height (incl. bracket) |
| | 379mm | 72mm | 232mm |
| Weight | | | |
| Model | Weight | | |
| Nexus LX/RF | 1.8kg | | |
| Construction | | | |
| Part | Construction | | |
| Body and diffuser | Polycarbonate | | |
| Bracket | White powder coated zinc steel | | |

| Light source | | |
|---------------------|---------------------|--|
| Model | Light source | |
| Nexus LX/RF | Multiple LED 0.7W | |

| Power consumption | | |
|--------------------------|--------------------------|--|
| Model | Power consumption | |
| Nexus LX/RF | 2.4W | |

Note: Preliminary results

| Photometrics | | | |
|---------------------|--------------|--|-----------------------|
| Model | Class | | Classification |
| Nexus LX/RF | C0 | | D3.2 |
| | C90 | | E2 |

Note: Preliminary results

Note:
- Designed to comply with AS2293 and meet relevant Australian EMC standards