

PRODUCT SPECIFICATION

# CTEGR3LS1-S22

## Guideway Self-Contained 22M IP40 Naveo Recess

Catalogue Number **CTEGR3LS1-S22**  
GID **7TCA091180R0254**  
Warranty **4 Year/s Refer to ABB warranty terms & conditions**  
Power Supply System **Self-Contained (individual battery)**  
Mounting Method/Form **Ceiling, Wall Recessed**  
Housing Material **Aluminium/Plastic**  
Colour **Silver**  
Dimensions (LxWxD) **235 x 84 x 134 mm**  
Temperature Range **5 to 35°C**  
Weight **1.2 Kg**

Emergency Duration (Hours) **3**  
Battery **NiMH**  
Monitoring Equipment **Naveo®Pro**  
Lamp **1 x 2W LED**  
Emergency Light Output (Lumens) **Not Applicable**  
Average Lifespan light source (Hours) **100000 Hours**  
Light Colour/Temperature/CRI **White / 5000 / 80**  
Degree of Protection **IP40**

Type of Legend **Single or Double Sided**  
Exit Sign Viewing/Recognition Distance (m) **22**  
Nominal Voltage **220-240v AC 50Hz**  
Power Consumption **4.4 VA / 4 Watts**  
Current **Nominal: 19mA (mA)**

### Accessories

**XEN2EG22** Down ISO7010 Legend Single Sided  
**XEN3EG22** Left ISO7010 Legend Single Sided  
**XEN6EG22** Right ISO7010 Legend Single Sided  
**XEN5EG22** Up ISO7010 Legend Single Sided  
**XBN1EG22** Arabic English Legend Single Sided  
**XEN0G22** Blank Legend Single Sided

**EG-T4EG** Cover Discs (2x semi-circular, 2x rectangular) for Slave

**EG-TKIT50** Suspension Kit Pendant 50mm  
**EG-TKIT100** Suspension Kit Pendant 100mm  
**EG-WKIT150** Wire Suspension Kit 150mm

**XEN602EG22** Down ISO7010 Legend Flag Mount  
**XEN603EG22** Left ISO7010 Legend Flag Mount  
**XEN606EG22** Right ISO7010 Legend Flag Mount  
**XEN605EG22** Up ISO7010 Legend Flag Mount



Exit Sign Suspended  
CTEGR3LS1-S22 + EG-WKIT150



Exit Sign Recessed  
CTEGR3LS1-S22

