


Temp.
0 25 40 50 60C



Shift index for long-time delay only.

MULTIPLES OF CIRCUIT BREAKER CURRENT RATING



Industrial Solutions

Current Ratings

60, 70 and 80 Amperes

Voltage Ratings

2 and 3 pole – 480 Vac (250 Vdc)

Frequency Rating

60 Hertz

Molded Case Circuit Breaker E 100 LINE

Type TED, 60-80 Amperes

Enclosure Compensated

Long-time Delay and Instantaneous

Time-current Curves

Curves show enclosure-compensated circuit breaker in open air, 40°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use shift index at top of sheet.

K215147

Adjustments

Long-time delay thermal trip: not adjustable.
Instantaneous magnetic trip: not adjustable.

NOTE: Limiters can only be applied to AC breakers.

by ABB