

**PANEL MARKS:**

**RNSB08L7245R**

**TECHNICAL SPECIFICATIONS**

PANEL TYPE: ReliaGear neXT SuperBox  
 QUANTITY: 1  
 AMPS: 800A  
 VOLTAGE: Up to 600V  
 SYSTEM: 3P3W or 3P4W  
 KAIC: Up to 200 KAIC SC FULLY RATED  
 MATERIAL: COPPER BUS  
 PLATE: SILVER PLATE  
 ENCLOSURE: NEMA 3R  
 MOUNTING: SURFACE

**MAIN DISCONNECT DEVICE**

FEED DIR. Bottom  
 TYPE: Lugs  
 AMPS: 800A  
 CATALOG NO.: LGML260A  
 POLES: 3  
 LUGS: Main Lug (4) #2-600 mcm, No Feed Through

**INTERIOR X-VALUES**



TOTAL X BUS AVAILABLE X BUS  
 24 20

**OPTIONS INCLUDED**

QTY	DESCRIPTION
1	Copper Bus Heat Rated
1	47 Ckt bonded grd

**BOM**

QTY	CAT #	DESCRIPTION
1	GDBG47AL	Ground
1	IN2408BL3H2	Bus
1	NL1210NSTNDAL	Neutral
1	ER7245R	Enclosure
1	IF2445F	Frame
1	FT45S00135	Front 1 of 2
1	FT45S00270	Front 2 of 2
1	GC45F24BLA	Gutter
1	BP45F	WirePost
6	LGML260A	MLO
5	SR03BF	Spacer
5	SR03BB	Spacer
2	SR02BF	Spacer
2	SR02BB	Spacer
1	SR01BF	Spacer
1	SR01BB	Spacer



<b>PANEL INFORMATION</b>	
INTERNAL DIMENSIONS	72"X47"X11"
NOTES	
EXTERNAL DIMENSIONS	73"X48.5"X16.7"

- FML - FRAME MOUNTING LOCATION.
  - DRAWING NOT TO SCALE.
  - DIMENSIONS ARE IN INCHES[mm].
- NEUTRAL CAN BE MOUNTED IN ANY CORNER

NEUTRAL ARE PRESSURE LUGS.

PROJECT NAME :	<b>ABB</b>	PANEL ID:	PRODUCT NAME:	DRAWING NO:
CUSTOMER:		CREATED BY:	ReliaGear neXT	ITEM NO:
		DATE:	PANELBOARD	MARKS:
		REVISION NO.		QUOTE NO:
				SHEET: