

Item	Qty.	Description	Price per unit	Amount
------	------	-------------	----------------	--------

		<p><b>Manual Call Point, blue, changeover contact</b></p> <p>The Manual Call Point HM/A 2.1 is designed for connection to a conventional DC threshold alarm detector zone. The Manual Call Point latches. A visual display indicates the Manual Call Point's state. The Manual Call Point possesses an additional changeover switch. The Manual Call Point can be used as a button simply by removing the locking lever. Both SM and FM cable entries are available for the cabling.</p> <p>Operating voltage 10 – 30 V DC (supplied by the zone)</p> <p>Contact load of switch S2 &lt; 25 V AC / 2 A or &lt; 60 V DC / 2 A</p> <p>Dimensions (W x H x D) 126 x 126 x 35 mm</p> <p>Connection Screw terminals Max. 1.5 mm<sup>2</sup></p> <p>Cable entry point Top and bottom 2 pcs. M20 x 1.5 mm Rear wall 2 pcs. 24 x 10 mm</p> <p>Weight 420 g</p> <p>Degree of protection IP43</p> <p>Rel. humidity 5 – 95% (non-condensing)</p> <p>Ambient temperature -20 to +60 °C (continuous operation, without icing) -25 to +70 °C (max. 12 hours)</p> <p>Manufacturer: ABB STOTZ-KONTAKT</p> <p><b>Type: HM/A 2.1</b></p> <p>Material:..... Labor:.....</p>	Carry:	
--	--	---	--------	--

		HMA_21_AT_EN_V2-0 9AKK107991A0090 Rev. A	Carry:	
--	--	---	--------	--

**HM/A 2.1**

**HM/A 2.1**