

VHA SPARES PARTS LIST

SL NO.	ARTICLE NO.	DESCRIPTION	PHOTO
1	IN21880001-3	HANDLE FOR SELECTOR	 <p data-bbox="1458 787 1567 814">IN2188001-3 HANDLE FOR SELECTOR</p>
2	IN21750003-DG	PROFILE ASSY	 <p data-bbox="1542 1060 1624 1081">IN21750003-E PROFILE ASSY</p>
3	IN21840005-12	ARM RIGHT	 <p data-bbox="1437 1323 1502 1354">IN21840005-12 ARM RIGHT</p>
4	IN21670002-A	SELECTOR FOR RACKING MECHANISM	 <p data-bbox="1437 1585 1559 1627">IN21670002-A SELECTOR FOR RACKING MECHANISM</p>
5	IN68870001-1	RACK IN HANDLE	 <p data-bbox="1518 1869 1607 1900">IN68870001-1 RACK IN HANDLE</p>

6	2657992-F	SLIDING CONTACT FOR SERVICE POSITION	 <p>2657992-F SLIDING CONTACT FOR SERVICE POSITION</p>
7	IN26533001-1	LIMIT SWITCH (L&T SS 0375)	 <p>IN26533001-1 LIMIT SWITCH (L&T SS 0375)</p>
8	IN53260001-1	LIMIT SWITCH (2NO)	 <p>IN53260001-1 LIMIT SWITCH (2NO)</p>
9	IN53260001-2	LIMIT SWITCH (1NO+1NC)	 <p>IN53260001-2 LIMIT SWITCH (1NO+1NC)</p>
10	IN26340002-M	UPPER MAIN CONTACTS 1250A	 <p>IN26340002-M UPPER MAIN CONTACTS 1250A</p>
11	IN26570001-H	LOWER MAIN CONTACTS 1600A/2000A	 <p>IN26570001-H LOWER MAIN CONTACTS 1600A/2000A</p>
12	IN26570001-D	LOWER/UPPER MAIN CONTACTS 2500A	 <p>IN26570001-D LOWER/UPPER MAIN CONTACTS 2500A</p>

20	IN21580003-AE	SHUTTER ASSLY.	 <p>IN21580003-AE SHUTTER ASSLY.</p>
21	IN21580002-18	GUIDE FOR SHUTTER	 <p>IN21580002-18 GUIDE FOR SHUTTER</p>
22	IN21580002-55	UPPER SMC PARTITION WITHOUT SHUTTERS	 <p>IN21580002-55 UPPER SMC PARTITION WITHOUT SHUTTERS</p>
23	1VYN402201-E	RACKING MECHANISM COMPLETE W/O.E.S.	 <p>1VYN402201-E RACKING MECHANISM COMPLETE W/O.E.S.</p>
24	1VYN402201-C	RACKING MECHANISM COMPLETE 12KV W.E.S.	 <p>1VYN402201-C RACKING MECHANISM COMPLETE 12KV W.E.S.</p>
25	1VYN402201-BZ	RACKING MECHANISM COMPLETE < 1250A, 24KV W/O E.S.	 <p>1VYN402201-BZ RACKING MECHANISM COMPLETE < 1250A, 24KV W/O E.S.</p>
26	IN52630001-Z	RACKING MECHANISM 3000A WITH E.S.	<p>IN52630001-Z RACKING MECHANISM 3000A WITH E.S.</p> <p>PHOTO PENDING</p>

27	1VYN402301-EE	RACKING MECHANISM 36KV VHA W/O E.S.	
28	1VYN402301-GH	RACKING MECHANISM 36KV WITH E.S. W/O. ELE.INTERLOCK	
29	IN55530001-1	STARTER FOR MOTOR	 <p data-bbox="1451 877 1620 905">IN55530001-1 STARTER FOR MOTOR</p>
30	IN22990001-1	ROLLER (WHEEL)	 <p data-bbox="1403 1146 1503 1169">IN22990001-1 ROLLER (WHEEL)</p>
31	IN21790001-5	RAIL PROFILE LEFT	 <p data-bbox="1507 1409 1604 1438">IN21790001-5 RAIL PROFILE LEFT</p>
32	IN21790001-6	RAIL PROFILE RIGHT	 <p data-bbox="1495 1682 1620 1707">IN21790001-6 RAIL PROFILE RIGHT</p>
33	IN21790001-11	RAIL PROFILE LEFT 24KV	 <p data-bbox="1503 1955 1604 1978">IN21790001-11 RAIL PROFILE LEFT 24KV</p>

34	IN21790001-12	RAIL PROFILE RIGHT 24KV	 <p>IN21790001-12 RAIL PROFILE RIGHT 24KV</p>
35	1VYN202250-020	TOP/BOTTOM MONOBLOCK BUSHING FOR 24 kV	 <p>1VYN202250-020 TOP/BOTTOM MONOBLOCK BUSHING FOR 24 kV</p>
36	1VYN402201-VP	Racking Mechanism for HPA breaker-3000A	 <p>1VYN402201-VP Racking Mechanism for HPA breaker-3000A</p>
37	1VYN402201-YD	Racking mechanism for Vacuum contractor	 <p>1VYN402201-YD Racking mechanism for Vacuum contractor</p>
38	IN52590001-A	EMERGENCY TRIP ASSLY	 <p>IN52590001-A EMERGENCY TRIP ASSLY</p>
39	1VYN402201-VZ	SHROUD ASSY	 <p>1VYN402201-VZ SHROUD ASSY</p>

40	2158423-BM1	UPPER PC PARTITION WITHOUT SHUTTERS (VHA 3150A)	PHOTO PENDING
41	2158423-BK1	LOWER PC PARTITION WITHOUT SHUTTERS (VHA 3150A)	PHOTO PENDING
42	1VYN402201-CB	RACKING MECHANISM COMPLETE >1600A, 24KV WITH E.S.	PHOTO PENDING
43	1VYN402201-F	RACKING MECHANISM >= 1600A W/O E.S.	PHOTO PENDING
44	1VYN402301-NJ	RACKING MECHANISM 36KV WITH E.S. AND CASTLE LOCK	PHOTO PENDING
45	IN21580001-N	SHUTTER ASSLY. FOR 24KV SF6	PHOTO PENDING

46

21584023-BD

SHUTTER (VHA 3150A)

PHOTO PENDING