

PRODUCT SPECIFICATION

# CTWWA3LS1X

## Weatherforce Self-Contained 27M IP65 Naveo Surface

Catalogue Number **CTWWA3LS1X**  
 GID **7TCA091180R0354**  
 Warranty **3 Year/s Refer to ABB warranty terms & conditions**  
 Power Supply System **Self-Contained (individual battery)**  
 Mounting Method/Form **Ceiling, Wall Surface**  
 Housing Material **Metal/plastic**  
 Colour **White**  
 Dimensions (LxWxD) **400 x 140 x 100 mm**  
 Temperature Range **0 to 30°C**  
 Weight **1.49 Kg**

Emergency Duration (Hours) **3 Hours**  
 Battery **NiCd**  
 Monitoring Equipment **Naveo®Pro**  
 Lamp **1 x 2W LED**  
 Emergency Light Output (Lumens) **207**  
 Average Lifespan light source (Hours) **100000 Hours**  
 Light Colour/Temperature/CRI **White / 4000 / 80**  
 Degree of Protection **IP65 IK10**

Type of Legend **Single or Double Sided**  
 Exit Sign Viewing/Recognition Distance (m) **27**  
 Nominal Voltage **220-240v AC 50/60Hz**  
 Power Consumption **6.1 VA / 3.9 Watts**  
 Current **Nominal: 25.5mA (mA) Inrush: 0.7A**

### Accessories

**XEN2/2DV32** Double sided Diffuser with Down+Down ISO7010 Legend  
**XEN3/6DV32** Double sided Diffuser with Left+Right ISO7010 Legend  
**XEN5/5DV32** Double sided Diffuser with Up+Up ISO7010 Legend

**XB10DV32** Double sided Diffuser with Blank+Arabic English Legend  
**XB11DV32** Double sided Diffuser with Arabic English+Arabic English Legend  
**XB23DV32** Double sided Diffuser with Arabic English Left+Arabic English Right Legend  
**XB50DV32** Double sided Diffuser with Blank+Arabic English Up Legend  
**XB66DV32** Double sided Diffuser with Arabic English Down+Arabic English Down Legend

**BBZ** Semi recessing bezel White



**Double Sided Exit Sign**  
 CTWWA3LS1X + XEN2/2DV32

