



CYKLOOLUX-HAL55.2/12

Self-contained 55 watt, non-maintained surface mount LV halogen lamp hand lamp, series Mobile

Product Information

Type	CYKLOOLUX-HAL55.2/12
Catalog number	11170004
Category_	Escape route lighting
GTIN	08713812005904
GID	7TCA091210R0001
Serie	Mobiel
Warranty (Year)	2



Characteristics

Power supply system	Self-contained individual battery
Continuous operation	No
Mounting Method	Wall
Mounting form	Surface
Material housing	Plastic
Colour housing	Gray
Material	Plastic
Colour	Gray
Length (mm)	400
Width (mm)	140
Height/depth (mm)	530
Nominal voltage (V)	230
Voltage type	AC
Duration (hours)	1
Battery	Lead
Monitoring equipment	None
With lamp	Yes
Lamp Type	LV halogen lamp
Lamp holder	Other
Lamp power (W)	55
Number of lamps	2
Light output in emergency operation (lm)	860
Colour of light	White
Protection class	I
Degree of protection (IP)	65
With remote switch connection	No
Wiring system	Non-maintained circuit
Type of indicator	Not applicable
Circuit	Other
Power consumption maintained mode (W)	12
Apparent power consumption maintained mode (VA)	15
Powerfactor	1
Temperature range (°C)	5 ~ +25

Article Details

Product class	Emergency luminaire
E-code	EC001957
Discount group	30912
Harmonized code	9405403100

GLN

8713812000008

Ordering information

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

Supply Information

Weight (kg)	12,34
Packaging	Bag
Packaging dimensions (LxWxH) (mm)	400 x 140 x 530